



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FPS6X88MTGX 22-26AWG Cat 6A Shielded RJ45 Plug *Panduit Corporation*

Catalog Number	FPS6X88MTGX
Manufacturer	Panduit Corporation
Description	The TX6A Category 6A Shielded RJ45 Field Term Plug Terminates 4-Pair, 22-26 Awg, 100 Ohm, Shielded Twisted Pair Cable and Is Backwards Compatible With Cat 6 and 5E. The Plug Utilizes TG Style Technology to Optimize Performance By Maintaining Cable Pair Geometry While Eliminating Conductor Untwist. This Plug Simplifies Installation Of Common Devices Such As Cameras and Wireless Access Points.
Weight per unit	0.2400 (lbs/each)
Product Category	Wiring Devices

Features

Cable Entry	T568A/T568B
media	Yes

Material, Color, and Finish

Color	Silver
-------	--------

Dimensions and Weight

Depth	NA
Width	0.54

Descriptions

Description	22-26AWG CAT 6A SHIELDED RJ45 PLUG
extra long description	PAN FPS6X88MTG-X TX6A Cat 6A Shield
Long Description	The TX6A Category 6A Shielded RJ45 Field Term Plug terminates 4-pair, 22-26 AWG, 100 ohm, shielded twisted pair cable and is backwards compatible with Cat 6 and 5e. The plug utilizes TG style technology to optimize performance by maintaining cable pair geometry while eliminating conductor untwist. This plug simplifies installation of common devices such as cameras and wireless access points.
Product Type	TX6A Cat 6A Shielded RJ45 Field Term Plug, 22-26 Awg

Manufacturer Information

Brand	Panduit®
GTIN	00613056579910
Manufacturers Part Number	FPS6X88MTG-X
UPC	613056579910

Taxonomies, Classifications, and Categories

Type	Shielded Field Term Plug
------	--------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Weight Per each	0.24

Uses, Certifications, and Standards

standard	Exceeds ANSI/TIA 568-C.2 Category 6A and ISO 11801 Class EA Channel performance requirements with up to two field term plugs in channel. Meets or exceeds proposed TIA Modular Plug Terminated Link requirements with up to two field term plugs in link, Meets
----------	---