



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FRNR200 200A 250V TD Class RK5 Dual Elem Fuse-Fusetron

Bussmann Fuses

Catalog Number	FRNR200
Manufacturer	Bussmann Fuses
Description	Time Delay Fusetron Fuse, RK5 Class Fuse, Dual Element Fuse, 10 S @ 500% Response Time, Blade End X Blade End Connection, 200 A, 250 V Ac;125 V DC, Blade Terminal, 1.56 In Diameter, 7.13 In Overall Length, 0.79 LB
Weight per unit	0.7900 (lbs/each)
Product Category	Dual Element

Features

amperage rating	200 A
class	RK-5
connection	Blade End X Blade End
element	Dual

Dimensions and Weight

Size	1.56 In Diameter X 7.13 In Length
------	-----------------------------------

Descriptions

Description	200A 250V TD CLASS RK5 DUAL ELEM FUSE-FUSETRON
-------------	--

Manufacturer Information

GTIN	00051712101899
sub brand	Fusetron
UPC	051712101899

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Current Limiting, Time Delay

Packaging

Carton	1
Weight Per each	0.79

Uses, Certifications, and Standards

standard	UL 248-12, CSA C22.2, CE
----------	--------------------------



Powering Business Worldwide

pe.eaton.com

FRN-R Fusetron

FRN-R-200

UPC:051712101899

Dimensions:

- **Height:** 1.56 IN
- **Length:** 7.13 IN
- **Width:** 1.56 IN

Weight:.9 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** Current-limiting, time delay
- **Application:** Combination starters, motor control centers, machinery disconnects, power panelboards
- **Voltage Rating:** 250 Vac, 125 Vdc
- **Amperage Rating:** 200A
- **Interrupt Rating:** 200 kAIC at 250 Vac, 20 kAIC at 125 Vdc
- **Class:** Class RK5
- **Connection:** Blade end X blade end
- **Packaging Type:** Standard
- **Diameter:** 1.56 IN
- **Fuse Indicator:** Non Indicating
- **Response Time:** 10s at 500%
- **Number Of Elements:** Dual

Supporting documents:

- [Product Catalog](#)
- [FUSETRON DUAL ELEMENT CLASS RK5](#)
- [Product Datasheet](#)

Certifications: No Data

Product compliance:

- CE Marked



