



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FRSR70 70A 600V TD Class RK5 Dual Elem Fuse-Fusetron

Bussmann Fuses

Catalog Number	FRSR70
Manufacturer	Bussmann Fuses
Description	Time Delay Fusetron Fuse, RK5 Class Fuse, Dual Element Fuse, 10 S @ 500% Response Time, Blade End X Blade End Connection, 70 A, 600 V Ac;300 V DC, Blade Terminal, 1.11 In Diameter, 7.88 In Overall Length, 0.4 LB
Weight per unit	0.4000 (lbs/each)
Product Category	Dual Element

Features

amperage rating	70 Watt
class	RK-5
connection	Blade End X Blade End
element	Dual

Dimensions and Weight

Size	1.11 In Diameter X 7.88 In Length
------	-----------------------------------

Descriptions

Description	70A 600V TD CLASS RK5 DUAL ELEM FUSE-FUSETRON
Special Features	Renewable

Manufacturer Information

GTIN	00051712508407
sub brand	Fusetron
UPC	051712508407

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Current Limiting, Time Delay

Packaging

Carton	1
Package	5
Weight Per each	0.4

Uses, Certifications, and Standards

standard	UL 248-12, CSA, CE
----------	--------------------



Powering Business Worldwide

pe.eaton.com

FRS-R Fusetron

FRS-R-70

UPC:051712508407

Dimensions:

- **Height:** 7.88 IN
- **Length:** 1.11 IN
- **Width:** 1.11 IN

Weight:.4 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** Current-limiting, time delay
- **Application:** Combination starters, motor control centers, machinery disconnects, power panelboards
- **Voltage Rating:** 600 Vac, 300 Vdc
- **Amperage Rating:** 70A
- **Interrupt Rating:** 200 kAIC at 600 Vac, 20 kAIC at 300 Vdc
- **Class:** Class RK5
- **Connection:** Blade end X blade end
- **Packaging Type:** Standard
- **Diameter:** 1.11 IN
- **Fuse Indicator:** Non Indicating
- **Response Time:** 10s at 500%
- **Number Of Elements:** Dual

Supporting documents:

- [Product Catalog](#)
- [FUSETRON DUAL ELEMENT FUSE CLASS RK5](#)
- [Product Datasheet](#)

Certifications: No Data

Product compliance:

- CE Marked



