

fan control with rotate on/off knob



- rotate on/off, rotate to adjust fan speed
- 3 quiet fan speeds for increased comfort
- designed to reduce motor hum
- for use with only one ceiling paddle fan

quiet 3-speed control

single pole	1.5A	FSQ-2F-
-------------	------	----------------

replacement knobs



- standard knob



- quiet, 3-speed fan control knobs

knobs

standard knob	RK-
3-speed fan control knob, white	280-324-01
3-speed fan control knob, ivory	280-324-06

fan controls with rotate on/off knob



- rotate on/off, rotate to adjust fan speed
- for use with multiple ceiling paddle fans or exhaust fans

fully variable control

single pole fan control	5A	FS-5F-
factory set minimum speed		
single pole fan control	5A	FS-5E-
user adjustable minimum speed		

See page 101 for available colors.
To order, add color suffix to model number.
Example: **FSQ-2F- WH**



Shown actual size: Rotary dimmer
and 1-gang Fassada® wallplate in ivory (IV)

available models

source type

- 💡 incandescent/halogen lighting
- ✂️ quiet 3-speed fan controls
- 🌀 fully variable fan controls

control locations

- 🔌 single pole (one location)
- 🔌🔌 3-way (two locations)

available colors (see page 12 for color swatches)

colors (gloss finish)

- WH** white
- IV** ivory

Rotary dimmers

product family features

- easy-turn knob adjusts light to your favorite level
- coordinating Fassada® wallplates available separately (including matte, gloss, and stainless steel finishes)
- **eco-dim®** model available

Questions on installation or selection?
Call Lutron® 24 hours/7 days a week at
1.800.523.9466 or visit www.lutron.com

fan control with rotate on/off knob



- rotate on/off, rotate to adjust fan speed
- 3 quiet fan speeds for increased comfort
- designed to reduce motor hum
- for use with only one ceiling paddle fan

quiet 3-speed control

single pole	1.5A	FSQ-2F-
-------------	------	----------------

replacement knobs



- standard knob



- quiet, 3-speed fan control knobs

knobs

standard knob	RK-
3-speed fan control knob, white	280-324-01
3-speed fan control knob, ivory	280-324-06

fan controls with rotate on/off knob



- rotate on/off, rotate to adjust fan speed
- for use with multiple ceiling paddle fans or exhaust fans

fully variable control

single pole fan control	5A	FS-5F-
factory set minimum speed		
single pole fan control	5A	FS-5E-
user adjustable minimum speed		

See page 101 for available colors.
To order, add color suffix to model number.
Example: **FSQ-2F- WH**



Shown actual size: Rotary dimmer
and 1-gang Fassada® wallplate in ivory (IV)

available models

source type

- 💡 incandescent/halogen lighting
- ✂️ quiet 3-speed fan controls
- 🌀 fully variable fan controls

control locations

- 🔌 single pole (one location)
- 🔌🔌 3-way (two locations)

available colors (see page 12 for color swatches)

colors (gloss finish)

- WH** white
- IV** ivory

Rotary dimmers

product family features

- easy-turn knob adjusts light to your favorite level
- coordinating Fassada® wallplates available separately (including matte, gloss, and stainless steel finishes)
- **eco-dim®** model available

Questions on installation or selection?
Call Lutron® 24 hours/7 days a week at
1.800.523.9466 or visit www.lutron.com