



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FXLEDST 69/97/132/168W Led Flood 4K/5K Trunion 120-277V *Rab Lighting*

Catalog Number	FXLEDST
Manufacturer	Rab Lighting
Description	Floodlights 10206-22010 Lumens Flexflood- Small Field Adjustable Power/CCT 69-97-132-168W Trunion Mount 5000K/4000K 120V-277V Bronze
Weight per unit	21.0 (lbs/each)
Product Category	Lighting

Features

amperage rating	120V:1.39
average life	100000
Ballast Type	LED Driver
Fixture Type	Flood Light
Lamp Type	LED
lumens	10206-22010
Power Rating	168
Shape	Rectangular
Voltage Rating	120/277
Wattage	69/132/168

Material, Color, and Finish

Finish	Bronze
housing color	Bronze
Housing Material	Die-Cast Aluminum

Dimensions and Weight

Height	8.94
Width	13.3

Descriptions

Description	69/97/132/168W LED FLOOD 4K/5K TRUNNION 120-277V
extra long description	RAB FXLEDST FA 168/132/97/69W 5/4KK
Long Description	Floodlights 10206-22010 Lumens Flexflood- Small Field Adjustable Power/Cct 69-97-132-168W Trunion Mount 5000K/4000K 120V-277V Bronze
Product Type	Fa 168/132/97/69W 5/4KK TRN BZ
Special Features	Field-adjustable Power/CCT



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	RAB Lighting Inc
GTIN	00192552019309
Manufacturers Part Number	FXLEDST
UPC	192552019309

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	FLOODLIGHT-Field Adjustable Power/CCT

Packaging

Carton	1
Weight Per each	21

Uses, Certifications, and Standards

Application	Outdoor
Enclosure	Dies-cast aluminum
environmental conditions	Suitable for wet locations. Suitable for mounting within 4 feet of the ground.
Mounting	TRUNNION
nema rating	6HX6V
standard	3G vibration rating per ANSI C136.31