



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



G022GR12D Start Stop *Hubbell--Killark*

Catalog Number	G022GR12D
Manufacturer	Hubbell--Killark
Description	Killark Go Series Operators Are A Component Use In Conjunction With A Hazardous Location Enclosure to Provide Control Solutions In For; Start/Stop Motor Functions, Led Pilot Light Indications and More. Utilized In Class 1 Division 1 & 2, Class 1 Zone 1 & 2 Areas For Indoor and Outdoor Use. UI Listed and Csa Certified.
Weight per unit	0.4000 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

action	Momentary
actuator	Double Pushbutton
amperage rating	10
Contact Configuration	1-NO/1-NC
Contact Rating	60A INRUSH @ 120 VAC; 30A INRUSH @ 240 VAC; 15A INRUSH @ 480 VAC; 12A INRUSH @ 600 VAC; 0.55A INRUSH @ 125 VDC; 0.275A INRUSH @ 250 VDC; 6A BREAKING @ 120 VAC; 3A BREAKING @ 240 VAC; 1.5A BREAKING @ 480 VAC; 1.2A BREAKING @ 600 VAC; 0.55A BREAKING @ 125 VDC; 0.275A BREAKING @ 250 VDC; 10A CARRYING @ 120 VAC; 10A CARRYING @ 240 VAC; 10A CARRYING @ 480 VAC; 10A CARRYING @ 600 VAC; 2.5A CARRYING @ 125 VDC; 2.5A CARRYING @ 250 VDC.
Poles	2
Voltage Rating	600 VAC maximum

Dimensions and Weight

Size	6.31 in x 2.25 in x 1.25 in
------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	START STOP
extra long description	KLRK GO22-GR12D PUSHBUTTON, DBL SHO
Long Description	Killark GO SERIES Operators are a component use in conjunction with a Hazardous Location enclosure to provide control solutions in for; START/STOP Motor Functions, LED Pilot Light Indications and more. Utilized in Class 1 Division 1 & 2, Class 1 Zone 1 & 2 areas for indoor and outdoor use. UL Listed and CSA Certified.
Product Type	Pushbutton, DBL Short Start/Stop
Special Features	Killark GO SERIES Operators are a component use in conjunction with a Hazardous Location enclosure to provide control solutions in for;START/STOP Motor Functions, LED Pilot Light Indications and more. Utilized in Class 1 Division 1 & 2, Class 1 Zone 1 & 2 areas for indoor and outdoor use. UL Listed and CSA Certified

Manufacturer Information

Brand	KILLARK
GTIN	00783936222882
Manufacturers Part Number	GO22-GR12D
series	GO
UPC	783936222882

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Push Button

Packaging

Carton	1
Weight Per each	0.4

Uses, Certifications, and Standards

Application	G Series custom control panel operators are designed for use in hazardous locations when installed in suitable enclosures such as B7E, EXB, XJB, DB, SWB, and GCS Series boxes and B7, Y7 starter enclosures.
environmental conditions	Hazardous locations
standard	UL, CSA