

# Specifications

## Eaton FWH-200B

Eaton Bussmann series FWH high speed fuse, 500 Vac/dc (UL), 200A, 200 kAIC at 300 Vdc, 50 kAIC at 300 Vdc, None, High speed fuse, Blade end X blade end, Class aR, Stud, White, Ceramic

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed cylindrical fuse
<b>CATALOG NUMBER</b>	FWH-200B
<b>UPC</b>	051712795869
<b>EAN</b>	5027590020916
<b>PRODUCT LENGTH/DEPTH</b>	91 mm
<b>PRODUCT HEIGHT</b>	30 mm
<b>PRODUCT WIDTH</b>	30 mm
<b>PRODUCT WEIGHT</b>	152 g
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	UL Recognized CSA Certified
<b>GLOBAL CATALOG</b>	FWH-200B



Powering Business Worldwide

## Product specifications

<b>AMPERAGE RATING</b>	200 A
<b>BREAKING CAPACITY</b>	200 kA
<b>FUSE INDICATOR</b>	Non Indicating
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>UTILIZATION CATEGORY</b>	aR (accompanied semiconductor protection)
<b>VOLTAGE TYPE</b>	AC/DC
<b>RATED SWITCHING CAPACITY</b>	200 kA
<b>RATED VOLTAGE AC</b>	500 V
<b>RATED VOLTAGE DC</b>	500 V
<b>MOUNTING DIMENSION</b>	M8
<b>CENTER-TO-CENTER DISTANCE OF CONNECTIONS</b>	74.09 mm
<b>CURRENT TYPE</b>	AC/DC
<b>CLASS</b>	Class aR
<b>CLEARING (I2T)</b>	8500
<b>WATT LOSSES</b>	40 W
<b>FUSE SHAPE</b>	Center bolted tags
<b>PRE ARC (I2T)</b>	1900
<b>COLOR</b>	White
<b>INTERRUPT RATING</b>	200 kAIC at 300 Vdc 50 kAIC at 300 Vdc
<b>CONNECTION</b>	Blade end x blade end
<b>CONSTRUCTION SIZE</b>	Other
<b>MATERIAL</b>	Ceramic
<b>MOUNTING METHOD</b>	Stud
<b>QUANTITY</b>	1
<b>VOLTAGE RATING</b>	500 Vac, 500 Vdc
<b>TYPE</b>	High speed fuse
<b>APPLICATION</b>	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
<b>FUSE TYPE</b>	FWH-B
<b>FUSE SYSTEM (ACCORDING TO IEC 60269)</b>	Other

## Resources

<b>CATALOGS</b>	<a href="#">eaton-bussmann-series-iec-high-speed-fuses-catalogue-ca135001en-en-gb.pdf</a> <a href="#">Bussmann series complete full line catalog no. 1007</a>
<b>MCAD MODEL</b>	<a href="#">eaton-hs-round-body-fuses-mcad-3d-models-fwh-125-200a-b.stp</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.