



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GAL445 4", 45D RGD Elb *Robroy/Ecn Korns*

Catalog Number	GAL445
Manufacturer	Robroy/Ecn Korns
Description	Standard Radius Elbow, 4 In Trade Size, Hot Dip Galvanized, 45 ° Connection Orientation, 16 In Bend Radius, External Threaded Connection, 2691 LB/100
Weight per unit	26.9 (lbs/each)
Product Category	Steel

Features

Applicable Standard	ANSI C80.1
Bend Angle	45 DEG
End Type	EXTERNAL THREADED
Material	Steel
Trade Size - Fractional	4 in
Trade Size in inch	4 in

Descriptions

Also Known As...	Elbow Pre-Fab Sweep
Commodity Description	Elbows, Couplings, Nipples, Running Thread - Steel
Description	4" RIGID 45D ELBOW

Manufacturer Information

Brand	EC-KORNS
GTIN	00784011001903
Model	GALELB
UPC	784011001903

Taxonomies, Classifications, and Categories

Category Description	RIGID ELBOWS
Type	STANDARD RADIUS

Packaging

Carton	1
Standard Package	BULK
Weight Per each	26.91

Uses, Certifications, and Standards

Approval	UL 6, CSA C22.2
----------	-----------------



RIGID STEEL COUPLINGS AND ELBOWS

UL Listed and Labeled

RIGID STEEL CONDUIT GALVANIZED COUPLINGS

CATALOG NUMBER	DESCRIPTION	WEIGHT PER 100 PIECES (lbs)	STANDARD CARTON
GALCPLG1/2	1/2" GALVANIZED COUPLINGS	12	100
GALCPLG3/4	3/4" GALVANIZED COUPLINGS	18	50
GALCPLG1	1" GALVANIZED COUPLINGS	31	50
GALCPLG1-1/4	1 1/4" GALVANIZED COUPLINGS	40	50
GALCPLG1-1/2	1 1/2" GALVANIZED COUPLINGS	52	50
GALCPLG2	2" GALVANIZED COUPLINGS	73	20
GALCPLG2-1/2	2 1/2" GALVANIZED COUPLINGS	179	12
GALCPLG3	3" GALVANIZED COUPLINGS	221	12
GALCPLG3-1/2	3 1/2" GALVANIZED COUPLINGS	355	12
GALCPLG4	4" GALVANIZED COUPLINGS	313	12
GALCPLG5	5" GALVANIZED COUPLINGS	432	BLK
GALCPLG6	6" GALVANIZED COUPLINGS	730	BLK

UL Listed and Labeled

RIGID CONDUIT STANDARD RADIUS ELBOWS

CATALOG NUMBER	DESCRIPTION	WEIGHT PER 100 PIECES (lbs)	STANDARD CARTON	RADIUS
GALELB1/2X90	1/2X90 GALVANIZED ELBOWS	75	50	4.25"
GALELB3/4X90	3/4X90 GALVANIZED ELBOWS	109	50	4.50"
GALELB1X90	1X90 GALVANIZED ELBOWS	189	25	5.75"
GALELB1-1/4X90	1 1/4X90 GALVANIZED ELBOWS	303	10	7.25"
GALELB1-1/2X90	1 1/2X90 GALVANIZED ELBOWS	416	15	8.25"
GALELB2X90	2X90 GALVANIZED ELBOWS	635	10	9.50"
GALELB2-1/2X90	2 1/2X90 GALVANIZED ELBOWS	1217	BLK	10.50"
GALELB3X90	3X90 GALVANIZED ELBOWS	1801	BLK	13.00"
GALELB3-1/2X90	3 1/2X90 GALVANIZED ELBOWS	2684	BLK	15.00"
GALELB4X90	4X90 GALVANIZED ELBOWS	3166	BLK	16.00"
GALELB5X90	5X90 GALVANIZED ELBOWS	6339	BLK	24.00"
GALELB6X90	6X90 GALVANIZED ELBOWS	10575	BLK	30.00"
GALELB1/2X45	1/2X45 GALVANIZED ELBOWS	64	50	4.25"
GALELB3/4X45	3/4X45 GALVANIZED ELBOWS	93	50	4.50"
GALELB1X45	1X45 GALVANIZED ELBOWS	161	25	5.75"
GALELB1-1/4X45	1 1/4X45 GALVANIZED ELBOWS	258	10	7.25"
GALELB1-1/2X45	1 1/2X45 GALVANIZED ELBOWS	354	15	8.25"
GALELB2X45	2X45 GALVANIZED ELBOWS	540	10	9.50"
GALELB2-1/2X45	2 1/2X45 GALVANIZED ELBOWS	1034	blk	10.50"
GALELB3X45	3X45 GALVANIZED ELBOWS	1531	blk	13.00"
GALELB3-1/2X45	3 1/2X45 GALVANIZED ELBOWS	2281	blk	15.00"
GALELB4X45	4X45 GALVANIZED ELBOWS	2691	blk	16.00"
GALELB5X45	5X45 GALVANIZED ELBOWS	5388	blk	24.00"
GALELB6X45	6X45 GALVANIZED ELBOWS	8989	blk	30.00"

NOTE: Weights shown are approximate for 90° elbows. To arrive at weights for 45° elbows deduct 15%.

Sizes 2-1/2 " and larger shipped in palletized cartons or bulk, thread protectors each end and ECN/Korns identifying label.