




GAR1629, Mechanical Grounding Connector, Cable to Rod or Pipe

By Burndy
Catalog # [GAR1629](#)

Mechanical Grounding Connector, Cable to Rod or Pipe, 2/0 AWG (Sol) -250 kcmil, 1-1/4" Pipe, 1-3/8"-1-1/2" Rod, #11 Rebar, Bright Dipped.



Application

For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Direct Burial Cable, Fence Post

General

EU RoHS Indicator	Yes
Installation Torque	240 Lb in
Recommended Run in-lb	
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Sub Brand	MECHANICAL CONNECTOR
Type	GAR
U Bolt Type	204
UPC	781810233603
UPC 12 Digit	7818102336033

Dimensions

Dimension - B Length inch	1.88 in
Dimension - Height fraction	3-1/2 in
Dimension - Height inch	3.50 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.51 in
Dimension - Outside Diameter inch	1.66 in
Dimension - Width fraction	3 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Conductor Related

Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Size	250 Kcmil
Conductor - Copper Str Size Range	1/0 AWG - 250 kcmil
Conductor - Copper Tube Std Size	1/4 IPS
Conductor - Copper Tube Std Size Range	1/4 IPS IPS
Conductor - Pipe or Round Tube Size Range	1-1/4 in
Conductor - Rebar Size	11
Conductor - Rebar Size Range	11
Conductor - Rod Size	1.380-1.66 in
Conductor - Rod Size Range	1 3/8 in-1 1/2 in
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size• CU Tube Std-Size• Rod-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - GAR1629_MODEL-IGES](#)
[3D Models - GAR1629_MODEL-PDF](#)
[3D Models - GAR1629_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD_015789-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-GAR1629-SPEC-EN | REV 8/2023