



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4509 Texoma Parkway  
75090-0000, TX Sherman  
Phone: 903-892-8041  
Fax: 903-892-8907



## **G1SDBSB Silicon BRZ GCLMP** *Nsi Industries*

Catalog Number	G1SDBSB
Manufacturer	Nsi Industries
Description	The Nsi G-1-SDB-SB Heavy Duty Bronze Ground Clamp For Direct Burial Grips On Pipes Between 1/2" to 1" In Diameter and Is Suitable For Direct Burial Applications. Ground Clamps Ending With Suffix -SB Come With Silicon Bronze Screws and A Cast Bronze Clamp Body. These Economical, High-Quality Metals Provide Durable Performance In A Range Of Applications and An Extended Life Over Stainless-Steel Components. UI Listed 467 For Grounding and Bonding. Stock Products You Can Rely On"Stock Nsi.
Weight per unit	0.2800 (lbs/each)
Product Category	Ground Rods & Grounding System

### **Features**

Material	Silicon Bronze
Warranty	1 YEAR

### **Material, Color, and Finish**

Clamp Material	Silicon Bronze
Color	Bronze
Insulation Color	Bronze
Insulation Material	Silicon Bronze

### **Dimensions and Weight**

Length	2.28
--------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4509 Texoma Parkway  
75090-0000, TX Sherman  
Phone: 903-892-8041  
Fax: 903-892-8907

## Descriptions

Description	SILICON BRZ GCLMP
extra long description	NSI G-1-SDB-SB Ground Clmp 1/2-1 IN
Features	NSI grounding and bonding products rise to the occasion in a wide variety of indoor and outdoor environments with excellent material quality and flexible designs. These cast bronze ground clamps offer a convenient and reliable solution for grounding electrical infrastructure in direct burial applications. Grips onto pipes tightly by using the silicon bronze screws to tighten the clamp and holds ground wire in place with a simple set-screw design. Additionally, NSI grounding clamps feature flexible sizing
Long Description	The NSI G-1-SDB-SB Heavy Duty Bronze Ground Clamp for Direct Burial grips on pipes between 1/2" to 1" in diameter and is suitable for direct burial applications. Ground clamps ending with suffix -SB come with silicon bronze screws and a cast bronze clamp body. These economical, high-quality metals provide durable performance in a range of applications and an extended life over stainless-steel components. UL Listed 467 for Grounding and Bonding. Stock products you can rely onâ€”stock NSI.
Product Type	Ground CLMP 1/2-1 In DB Rated
Special Features	UL 486D Listed

## Manufacturer Information

Brand	Polaris
GTIN	00662381009937
Manufacturers Part Number	G-1-SDB-SB
UPC	662381009937

## Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Heavy Duty Direct Burial Ground Clamp

## Packaging

Carton	1
Weight Per each	0.28

## Uses, Certifications, and Standards

Application	Grounding Wire
standard	cULus