



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **GBC220 2-14SWG 20CKT Isolated GRND Bar** *Nsi Industries*

Catalog Number	GBC220
Manufacturer	Nsi Industries
Description	The Nsi GBC2-20 Copper Isolated Ground Bar Mounts Onto Most Surfaces Using The High-Strength Glass-Filler Polyester Base, Then Fits Up to 20 Copper Cables In The 2 to 14 Awg Size Range. The High-Conductivity Copper Body Is Rated For Use With Copper Wiring and Forms Reliable Connections Using The Simple Tightening Screw Lug Design. Stock Products You Can Rely Onâ€”Stock Nsi.
Weight per unit	1.4 (lbs/each)
Product Category	Ground Rods & Grounding System

### **Features**

Conductor Size	2-14 AWG
insulation	Glass Filled Polyester Base
Voltage Rating	600 V
Warranty	1 YEAR

### **Material, Color, and Finish**

Conductor Material	Copper
--------------------	--------

### **Dimensions and Weight**

Length	8.04
Size	2-14 AWG



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	2-14SWG 20CKT ISOLATED GRND BAR
extra long description	NSI GBC2-20 Ground Bar CU 20 Circui
Features	NSI grounding and bonding products rise to the occasion in a wide variety of professional environments with excellent material quality and flexible designs. These copper isolated grounding bars offer a convenient and reliable solution for grounding multiple copper cables. The high-conductivity copper bar and high-strength glass-filled polyester base are both designed for long-lasting performance in a variety of environments. Designed to fit a range of different wire sizes by using a screw lug design, these
Long Description	The NSI GBC2-20 Copper Isolated Ground Bar mounts onto most surfaces using the high-strength glass-filler polyester base, then fits up to 20 copper cables in the 2 to 14 AWG size range. The high-conductivity copper body is rated for use with copper wiring and forms reliable connections using the simple tightening screw lug design. Stock products you can rely onâ€”stock NSI.
Product Type	Ground Bar Cu 20 Circuit 2-14
Special Features	Copper Bar With Isolation Base - 20 Circuits

## Manufacturer Information

Brand	NSi
GTIN	00662381010773
Manufacturers Part Number	GBC2-20
UPC	662381010773

## Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Isolated Ground Bars

## Packaging

Carton	1
Weight Per each	1.4

## Uses, Certifications, and Standards

Application	Grounding Wire
-------------	----------------