

ELLIOTT ELECTRIC SUPPLY 10440 Airline Highway 70816-0000, LA Baton Rouge Phone: 225-292-7746 Fax: 225-292-7840



GAR2026 4-2/0CU 3ips Burndy LLC

Catalog Number	GAR2026
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 4 Awg (Sol)-2/0 Awg (STR), 3" Pipe, 3"-3-1/2" Rod, Bright Dipped.
Weight per unit	1.7 (lbs/each)
Product Category	Large Terminals & Connectors
aturas	

Features

Material	COPPER ALLOY
pallet quantity	975

Descriptions

Description	4-2/0CU 3IPS
extra long description	BUR GAR2026 4-2/0CU 3IPS
Long Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 4 AWG (Sol)-2/0 AWG (Str), 3" Pipe, 3"-3-1/2" Rod, Bright Dipped.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Especially Good For Fence Posts, High Copper Alloy Cast Body With DURIUM U-Bolts, Nuts And Lockwashers, Permit Entire Connection To Be Buried In Ground Or Concrete Without Danger Of Corrosion, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial, Ground Rod Size: 3 - 3-1/2 IN, Tube (ips) Size: 3 IN, Width: 4-3/4 IN, Installation Torque: 240 IN-LB, Height: 5-5/8 IN

Manufacturer Information

Brand	BURNDY	
GTIN	00781810236406	
Manufacturers Part Number	GAR2026	
UPC	781810236406	

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding
	Fittings & Ground Rods
Туре	GAR
Dackaning	

Packaging

-··-g···g		
Carton	1	
Package	15	
Weight Per each	1.7	

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10440 Airline Highway 70816-0000, LA Baton Rouge Phone: 225-292-7746 Fax: 225-292-7840

Uses, (Certificatio	ns, and	Standards
---------	--------------	---------	------------------

Application	For Joining A Range Of Cable, Parallel Or At Right Angles To Rod
	Or Tube, Direct Burial Cable, Fence Post
standard	UL467