



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GAR6426 2/0AWG Ground Conn

Burndy LLC

Catalog Number	GAR6426
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 4 Awg (Sol)-2/0 Awg (STR), 3/8" Pipe, 5/8"-3/4" Rod, #5-#6 Rebar, Bright Dipped.
Weight per unit	0.5880 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	COPPER ALLOY
pallet quantity	2400

### Descriptions

Description	2/0AWG GROUND CONN
extra long description	BUR GAR6426 4-2/0CU 3/8IPS
Long Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 4 AWG (Sol)-2/0 AWG (Str), 3/8" Pipe, 5/8"-3/4" Rod, #5-#6 Rebar, Bright Dipped.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Especially Good For Fence Posts, High Copper Alloy Cast Body With DURIUM U-Bolts, Nuts And Lockwashers, Permit Entire Connection To Be Buried In Ground Or Concrete Without Danger Of Corrosion, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial, Height: 2-7/8 IN, Ground Rod Size: 5/8 - 3/4 IN, Tube (ips) Size: 3/8 IN, Width: 2-1/8 IN, Rebar Size: #5 (5/8 IN) - #6 (3/4 IN),

### Manufacturer Information

Brand	BURNDY
GTIN	00781810238202
Manufacturers Part Number	GAR6426
UPC	781810238202

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GAR

### Packaging

Carton	1
Weight Per each	0.588



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

For Joining A Range Of Cable, Parallel Or At Right Angles To Rod  
Or Tube, Direct Burial Cable, Fence Post

standard

UL467