## Specifications







## Eaton GDB-10A

Eaton GDB Series Fast-acting fuse, 10A, 250 Vac or less, 32 Vdc (self certified)

General specifications	
PRODUCT NAME	Eaton Bussmann series GDB fast-acting fuse
CATALOG NUMBER	GDB-10A
UPC	051712431866
PRODUCT HEIGHT	20 mm
PRODUCT DIAMETER	5.2 mm
PRODUCT WEIGHT	0.7 g
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant CCC Marked
CERTIFICATIONS	VDE
GLOBAL CATALOG	GDB-10A



Product specifications	
AMPERAGE RATING	10 A
FREQUENCY RATING - MAX	50 Hz
FREQUENCY RATING - MIN	50 Hz
VOLTAGE DROP	120 mV maximum
INTERRUPT RATING	35 AIC at 250 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
MATERIAL	Glass tube Nickel-plated brass end cap construction
QUANTITY	5
VOLTAGE RATING	250 Vac or less, 32 Vdc (self certified)
ТҮРЕ	Electronic
APPLICATION	Electronic circuits

	rces	Reso
Eaton Specification Sheet - GDB-10A		
	ATIONS AND	SPECIF
Eaton GDB fast-acting	EETS	DATAS
glass tube fuses data	-	
sheet		
GDB-10A  Eaton GDB fast-acting glass tube fuses data		

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



**Eaton Corporation plc** Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Follow us on social media to get the latest product and support information.











## Specifications







## Eaton GDB-10A

Eaton GDB Series Fast-acting fuse, 10A, 250 Vac or less, 32 Vdc (self certified)

General specifications	
PRODUCT NAME	Eaton Bussmann series GDB fast-acting fuse
CATALOG NUMBER	GDB-10A
UPC	051712431866
PRODUCT HEIGHT	20 mm
PRODUCT DIAMETER	5.2 mm
PRODUCT WEIGHT	0.7 g
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant CCC Marked
CERTIFICATIONS	VDE
GLOBAL CATALOG	GDB-10A



Product specifications	
AMPERAGE RATING	10 A
FREQUENCY RATING - MAX	50 Hz
FREQUENCY RATING - MIN	50 Hz
VOLTAGE DROP	120 mV maximum
INTERRUPT RATING	35 AIC at 250 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
MATERIAL	Glass tube Nickel-plated brass end cap construction
QUANTITY	5
VOLTAGE RATING	250 Vac or less, 32 Vdc (self certified)
ТҮРЕ	Electronic
APPLICATION	Electronic circuits

	rces	Reso
Eaton Specification Sheet - GDB-10A		
	ATIONS AND	SPECIF
Eaton GDB fast-acting	EETS	DATAS
glass tube fuses data	-	
sheet		
GDB-10A  Eaton GDB fast-acting glass tube fuses data		

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



**Eaton Corporation plc** Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Follow us on social media to get the latest product and support information.









