



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9707 Broadway St Suite 100
78217-0000, TX San Antonio
Phone: 210-646-6950
Fax: 210-646-6192



GHB2080 Type GHB BRKR 2P 80A 277/480VAC Max 125/250VDC Max *Eaton Corp*

| | |
|------------------|---|
| Catalog Number | GHB2080 |
| Manufacturer | Eaton Corp |
| Description | Eaton Series C Complete Molded Case Circuit Breaker, G-Frame, GHB, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Two-Pole, 80 A, 480Y/277 Vac, 125/250 VDC, 50/60 HZ |
| Weight per unit | 1.3 (lbs/each) |
| Product Category | 2 Pole |

Features

| | |
|----------------|-----------------------------------|
| Current Rating | 80 A |
| dimensions | 2.6300 IN X 2.0000 IN X 4.0000 IN |
| frame | G |
| Poles | 2 |
| Voltage Rating | 480Y/277 Vac, 125/250 Vdc |

Descriptions

| | |
|------------------------|---|
| Description | TYPE GHB BRKR 2P 80A 277/480VAC MAX 125/250VDC MAX |
| extra long description | ETN GHB2080 GHB CB 2P 80A 277/480VA |
| Features | Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A. |
| Long Description | Eaton Series C complete molded case circuit breaker, G-frame, GHB, Complete breaker, Fixed thermal, Fixed magnetic trip type, Two-pole, 80 A, 480Y/277 Vac, 125/250 Vdc, 50/60 Hz |
| Product Type | GHB CB 2P 80A 277/480VAC Max 125/250VDC |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | EATON CUTLER-HAMMER |
| GTIN | 00786679111178 |
| Manufacturers Part Number | GHB2080 |
| UPC | 786679111178 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS |
| Type | Molded case circuit breaker |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9707 Broadway St Suite 100
78217-0000, TX San Antonio
Phone: 210-646-6950
Fax: 210-646-6192

Packaging

Carton 1

Weight Per each 1.3

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies and
EOEMs - Other

standard UL Listed, Federal Specifications Classification W-C375B