



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GL40N #4/0 Cu CMPRSN Lug *Nsi Industries*

Catalog Number	GL40N
Manufacturer	Nsi Industries
Description	2 Hole Short Barrel Copper Compression Lug W/ Peep Hole 4/0 Awg - 1/2" Bolt Short Barrel Copper Compression Lugs With Peep Hole Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	0.2300 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Cable Size	4/0 AWG (STR)
Material	Copper
Number of Holes	2
Stud Size	1/2
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Purple
Finish	Tin Plated

Dimensions and Weight

Size	L=4.29 - W=1.00 - OD=.690 - ID=.550
------	-------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	#4/0 CU CMPRSN LUG
extra long description	NSI GL40N CMP Lug Cu Short 4/0 AWG
Features	2 Hole Short Barrel Copper Compression Lug w/ Peep Hole 4/0 AWG - 1/2" Bolt Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	2 Hole Short Barrel Copper Compression Lug w/ Peep Hole 4/0 AWG - 1/2" Bolt Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	CMP Lug Cu Short 4/0 Awg Nema MTG SPC
Special Features	4/0 AWG (STR) - 1/2 Mounting Holes - 1 3/4 Hole Spacing

Manufacturer Information

Brand	Polaris
GTIN	00662381036520
Manufacturers Part Number	GL40N
UPC	662381036520

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - Two Hole

Packaging

Carton	1
Weight Per each	0.23

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/2 Mounting Holes
standard	UL486A/B