



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GFTCB130 1P 30A Self-Test Ground Fault Breaker

Eaton Corp

Catalog Number	GFTCB130
Manufacturer	Eaton Corp
Description	Eaton BR Gfci Circuit Breaker, Ground Fault Circuit Breaker, 30 A, 10 Kaic, Single-Pole, 120/240 V, GFTCB, Ground Fault Circuit Interrupter, GFI, 5 Ma
Weight per unit	0.5000 (lbs/each)
Product Category	In Circuit Breakers

Features

amperage rating	30 A
dimensions	0.1000 IN X 0.1000 IN X 0.1000 IN
interrupt rating	10
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	1P 30A SELF-TEST GROUND FAULT BREAKER
extra long description	ETN GFTCB130 Eaton BR GFCI circuit
Features	Eaton's residential BR Circuit Breakers are used in load centers, panelboards, or similar devices. They are made for a wide range of applications and include: BR 1" circuit breakers and accessories for BR-style load centers; arc fault circuit interrupters (AFCI); and ground fault circuit interrupters (GFCI).
Long Description	Eaton BR GFCI circuit breaker,Ground fault circuit breaker,30 A,10 kAIC,Single-pole,120/240 V,GFTCB,Ground fault circuit interrupter,GFI,5 mA
Product Type	Eaton BR Gfci Circuit Breaker

Manufacturer Information

Brand	Eaton
GTIN	00786680129797
Manufacturers Part Number	GFTCB130
UPC	786680129797

Taxonomies, Classifications, and Categories

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	GFCI circuit breakers

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	20
Weight Per each	0.5

Uses, Certifications, and Standards

Application	Generation - Conventional Energy - Conventional EnergyGeneration - Renewable Energy - Alternative EnergyMarine Vessels and Equipment - Marine Vessels and Equipment - OtherOtherDatacenters - IT Space: CI and Hyper Converged
standard	UL 943,UL 489