



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GL6N141 #6 2H Cu SHRT CMP Lug

*Nsi Industries*

|                  |  |
|------------------|--|
| Catalog Number   | GL6N141  |
| Manufacturer     | Nsi Industries   |
| Description      | 2HOLESHORT Barrel Copper Compression Lug W/<br>PEEPHOLE6AWG-1/4" Bolt Short Barrel Copper Compression Lugs<br>With Peepholeis A Type Of Copper Compression Connector That<br>Is Produced From High Conductivity Copper Tubing. They Are<br>Tin-Plated to Provide Corrosion Resistance and Are Marked With<br>Die Index and Color Coded For Easy Reference. Listed For 35KV<br>Maximum When Properly Installed. |
| Weight per unit  | 4.0 (lbs/each)   |
| Product Category | Large Terminals & Connectors   |

### Features

|                 |               |
|-----------------|---------------|
| Cable Size      | # 6 AWG (STR) |
| Material        | Copper        |
| Number of Holes | 2             |
| Stud Size       | 1/4           |
| Voltage Rating  | 600 V         |
| Warranty        | 1 YEAR        |

### Material, Color, and Finish

|        |            |
|--------|------------|
| Color  | Blue       |
| Finish | Tin Plated |

### Dimensions and Weight

|      |                                     |
|------|-------------------------------------|
| Size | L=2.09 - W=.420 - OD=.300 - ID=.200 |
|------|-------------------------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | #6 2H CU SHRT CMP LUG  |
| extra long description | NSI GL6N-141 CU CMP Lug Short 6 AWG  |
| Features               | 2HoleShort Barrel Copper Compression Lug w/<br>PeepHole6AWG-1/4" Bolt Short Barrel Copper Compression Lugs<br>with PeepHoleis a type of copper compression connector that is<br>produced from high conductivity copper tubing. They are<br>tin-plated to provide corrosion resistance and are marked with<br>die index and color coded for easy reference. Listed for 35KV<br>maximum when properly installed. |
| Long Description       | 2HoleShort Barrel Copper Compression Lug w/<br>PeepHole6AWG-1/4" Bolt Short Barrel Copper Compression Lugs<br>with PeepHoleis a type of copper compression connector that is<br>produced from high conductivity copper tubing. They are<br>tin-plated to provide corrosion resistance and are marked with<br>die index and color coded for easy reference. Listed for 35KV<br>maximum when properly installed. |
| Product Type           | Cu CMP Lug Short 6 Awg 1/4 Bolt 5/8 Spac   |
| Special Features       | # 6 AWG (STR) - 1/4 Mounting Holes - 5/8 Hole Spacing  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00662381338006 |
| Manufacturers Part Number | GL6N-141       |
| UPC                       | 662381338006   |

## Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type                 | Short Barrel - Two Hole           |

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 100 |
| Weight Per each | 4   |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Terminate, Splice, Tap Power Connectors |
| environmental conditions | 90 C                                    |
| Mounting                 | 1/4 Mounting Holes                      |
| standard                 | UL486A/B, UL467 (8 AWG -3/0 AWG)        |