



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

221 Hord St
70123-0000, LA Harahan
Phone: 504-264-9995
Fax: 504-264-5996



GMA3A 3A 250V Fa Glass Fuse

Edison Fuses

Catalog Number	GMA3A
Manufacturer	Edison Fuses
Description	Miniature Fuse, Glass Tube Type; 20 Millimeter; UI 248-14, Csa, Ce, Pse Approval; 250 Volt Ac Voltage Rating; 5 Millimeter Diameter; 100 Amp At 250 Volt Ac, 10000 Amp At 125 Volt Ac Interrupting Rating; 3 Amp Current Rating; Ferrule Terminal Type
Weight per unit	0.0040 (lbs/each)
Product Category	Small Dimension Fuses

Features

Characteristics	FAST ACTING
Current Rating	3 Amp
Interrupting Rating	100 Amp at 250 Volt AC, 10000 Amp at 125 Volt AC
Terminal Type	Ferrule
Voltage Rating	250 Volt AC

Dimensions and Weight

Diameter	5 Millimeter
Length	20 Millimeter

Descriptions

Additional Information	Endcap Material Nickel Plated Brass; Application Electronic Circuit
Commodity Description	SMALL DIMENSION FUSES
Description	3A 250V FA GLASS FUSE
Long Description	MINIATURE FUSE, GLASS TUBE TYPE; 20 MILLIMETER; UL 248-14, CSA, CE, PSE APPROVAL; 250 VOLT AC VOLTAGE RATING; 5 MILLIMETER DIAMETER; 100 AMP AT 250 VOLT AC, 10000 AMP AT 125 VOLT AC INTERRUPTING RATING; 3 AMP CURRENT RATING; FERRULE TERMINAL TYPE
Product Type	Miniature Fuse

Manufacturer Information

Brand	Edison Fuses
Manufacturers Part Number	GMA-3A
Model	GMA

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	GLASS TUBE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

221 Hord St
70123-0000, LA Harahan
Phone: 504-264-9995
Fax: 504-264-5996

Availability

Manufacturer Status	Non-Stock
Status	Inactive

Packaging

Carton	1
Package	5
Weight Per each	0.004

Uses, Certifications, and Standards

Approval	UL 248-14, CSA, CE, PSE
----------	-------------------------