



GL35048 350MCM 1-Hole Compression Lug 1/2" Bolt

Nsi Industries

| | |
|------------------|---|
| Catalog Number | GL35048 |
| Manufacturer | Nsi Industries |
| Description | 1 Hole Short Barrel Copper Compression Lug W/ Peep Hole 350 MCM - 1/2" Bolt Short Barrel Copper Compression Lugs With Peep Hole Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed. |
| Weight per unit | 0.1900 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|-----------------|---------------|
| Cable Size | 350 MCM (STR) |
| Material | Copper |
| Number of Holes | 1 |
| Stud Size | 1/2 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|--------|------------|
| Color | Red |
| Finish | Tin Plated |

Dimensions and Weight

| | |
|------|-------------------------------------|
| Size | L=2.61 - W=1.28 - OD=.870 - ID=.700 |
|------|-------------------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3315 Park Place
75462-0000, TX Paris
Phone: 903-784-1916
Fax: 903-784-0107

Descriptions

| | |
|------------------------|---|
| Description | 350MCM 1-HOLE COMPRESSION LUG 1/2" BOLT |
| extra long description | NSI GL35048 CU CMP Lug Short 350 MC |
| Features | 1 Hole Short Barrel Copper Compression Lug w/ Peep Hole 350 MCM - 1/2" Bolt Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed. |
| Long Description | 1 Hole Short Barrel Copper Compression Lug w/ Peep Hole 350 MCM - 1/2" Bolt Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed. |
| Product Type | Cu CMP Lug Short 350 MCM 1/2 Bolt Size |
| Special Features | 350 MCM (STR) - 1/2 Mounting Hole |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSI |
| GTIN | 00662381036162 |
| Manufacturers Part Number | GL35048 |
| UPC | 662381036162 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Short Barrel - One Hole |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 0.19 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Terminate, Splice, Tap Power Connectors |
| environmental conditions | 90 C |
| Mounting | 1/2 Mounting Hole |
| standard | UL486A/B |