



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GL456 4AWG 5/16"BLT 1H Short BRL Cu CMP Lug

*Nsi Industries*

Catalog Number	GL456
Manufacturer	Nsi Industries
Description	1 Hole Short Barrel Copper Compression Lug W/ Peep Hole 4 Awg - 5/16" Bolt Short Barrel Copper Compression Lugs With Peep Hole Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	2.1 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Cable Size	# 4 AWG (STR)
Material	Copper
Number of Holes	1
Stud Size	5/16
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Gray
Finish	Tin Plated

### Dimensions and Weight

Size	L=1.50 - W=.490 - OD=.340 - ID=.250
------	-------------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	4AWG 5/16"BLT 1H SHORT BRL CU CMP LUG
extra long description	NSI GL456 CMP Lug Cu Short 4 AWG 5/
Features	1 Hole Short Barrel Copper Compression Lug w/ Peep Hole 4 AWG - 5/16" Bolt Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	1 Hole Short Barrel Copper Compression Lug w/ Peep Hole 4 AWG - 5/16" Bolt Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	CMP Lug Cu Short 4 Awg 5/16 Bolt Size
Special Features	# 4 AWG (STR) - 5/16 Mounting Hole

## Manufacturer Information

Brand	Nsi Industries
GTIN	00662381036032
Manufacturers Part Number	GL456
UPC	662381036032

## Taxonomies, Classifications, and Categories

Type	Short Barrel - One Hole
------	-------------------------

## Packaging

Carton	1
Weight Per each	2.1

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	5/16 Mounting Hole
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)