



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GL4N141 4AWG, 1/4BLT 2H, 5/8SPC Cu CMP Lug

Nsi Industries

Catalog Number	GL4N141
Manufacturer	Nsi Industries
Description	2 Hole Short Barrel Copper Compression Lug W/ Peep Hole 4 Awg - 1/4" Bolt Short Barrel Copper Compression Lugs With Peep Hole Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	5.0 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Cable Size	# 4 AWG (STR)
Material	Copper
Number of Holes	2
Stud Size	1/4
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Gray
Finish	Tin Plated

Dimensions and Weight

Size	L=2.09 - W=.490 - OD=.340 - ID=.250
------	-------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	4AWG,1/4BLT 2H,5/8SPC CU CMP LUG
extra long description	NSI GL4N-141 CMP Lug Cu Sht 4 AWG 1
Features	2 Hole Short Barrel Copper Compression Lug w/ Peep Hole 4 AWG - 1/4" Bolt Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	2 Hole Short Barrel Copper Compression Lug w/ Peep Hole 4 AWG - 1/4" Bolt Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	CMP Lug Cu SHT 4 Awg 1/4 BLT 5/8 SPC
Special Features	# 4 AWG (STR) - 1/4 Mounting Holes - 5/8 Hole Spacing

Manufacturer Information

Brand	Polaris
GTIN	00662381338020
Manufacturers Part Number	GL4N-141
UPC	662381338020

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - Two Hole

Packaging

Carton	0
Weight Per each	5

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/4 Mounting Holes
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)