



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GLL610C 2"GRND BSH 1/0-8AWG Lug

Crouse-Hinds

Catalog Number	GLL610C
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series GLL Grounding Bushing, Rigid/Imc, Copper Lug, #1/0-8 Awg, Malleable Iron, 105°C Temperature Rating, Threaded, 2"
Weight per unit	0.4000 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	Threaded
dimensions	2.7500 IN X 2.7500 IN X 0.8800 IN
Material	Malleable Iron Body, Plastic Throat Liner

### Dimensions and Weight

Size	2 in
------	------

### Descriptions

Description	2"GRND BSH 1/0-8AWG LUG
extra long description	MIDWEST GLL6 10C 2 GRND BUSH 105C I
Features	Crouse-Hinds series grounding bushings are used with threaded and threadless rigid/IMC conduit to provide a means of grounding conduit through an insulated bushing.
Long Description	Eaton Crouse-Hinds series GLL grounding bushing, Rigid/IMC, Copper lug, #1/0-8 AWG, Malleable iron, 105°C temperature rating, Threaded, 2"
Product Type	2 GRND Bush 105C Insul 1 to 8 Copp Lug
Special Features	With 8 To 1/0 AWG Copper Lug for Copper Grounding Conductor, Weight 40 Lb per 100

### Manufacturer Information

Brand	Eaton
GTIN	00784564123466
Manufacturers Part Number	GLL6 10C
UPC	784564123466

### Taxonomies, Classifications, and Categories

Category Description	COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS
Type	Grounding bushing

### Packaging

Carton	10
Weight Per each	0.4



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL, CSA
Temperature Rating	105 DEG C