



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1461 Technology Pkwy  
30165-0000, GA Rome  
Phone: 706-622-4953  
Fax: 706-622-4954



## GRP1150 11" 50LB Natural CBL Tie

*Nsi Industries*

Catalog Number	GRP1150
Manufacturer	Nsi Industries
Description	The Powergrp GRP-1150 100-Count Resealable Pack Of Type 21S Ah-2 Natural-Colored General-Purpose Cable Ties Are 11" Long, With 50LB Of Tensile Strength For Professional Applications. They're Made From Polyamide 6, 6 Nylon, Resulting In A High Mechanical Strength and A Wide Temperature Range (-40 F to 185 F). Fasten These 11" Cables Ties Around A Wide Range Of Equipment With A Bundle Diameter Between .08" (2MM) to 2.99" (76MM), Using The Bent Tips and Serrated Locking Mechanism to Form An Effortless An
Weight per unit	1.3 (lbs/each)
Product Category	Tools & Testers

### Features

Warranty	1 YEAR
----------	--------

### Material, Color, and Finish

Finish	Natural
--------	---------

### Descriptions

Description	11" 50LB NATURAL CBL TIE
extra long description	NSI GRP-1150 Cable Tie 11 IN 50Lb N
Features	PowerGRP cable ties are a comprehensive product line of specialty ties, strong enough to handle industrial environments and ideally suited for demanding applications. The GRP-1150 ties combine a self-locking design with a general purpose 50lb tensile strength rating, guaranteeing that these ties won't break easily. The GRP in our name stands for Guaranteed Rugged and Powerful, just one way we show that we're fully committed to building strong ties for professional users. GRP-1150 ties are waterproof an
Long Description	The PowerGRP GRP-1150 100-Count Resealable Pack of Type 21S AH-2 Natural-Colored General-Purpose Cable Ties are 11" long, with 50lb of tensile strength for professional applications. They're made from polyamide 6,6 nylon, resulting in a high mechanical strength and a wide temperature range (-40 F to 185 F). Fasten these 11" cables ties around a wide range of equipment with a bundle diameter between .08" (2mm) to 2.99" (76mm), using the bent tips and serrated locking mechanism to form an effortless an
Product Type	Cable Tie 11 In 50LB Nat (100PK)



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1461 Technology Pkwy  
30165-0000, GA Rome  
Phone: 706-622-4953  
Fax: 706-622-4954

## Manufacturer Information

Brand	Powergrp
GTIN	00662381009166
Manufacturers Part Number	GRP-1150
UPC	662381009166

## Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
----------------------	--

## Packaging

Carton	1
Package	100
Weight Per each	1.26

## Uses, Certifications, and Standards

standard	UL62275
Temperature Rating	-40F to 185F