



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## GRP818X 8" 18LB Bulk Natural CBL Tie

*Nsi Industries*

Catalog Number	GRP818X
Manufacturer	Nsi Industries
Description	The Powergrp GRP-818X 1000-Count Bulk Resealable Pack Of Type 21 Natural-Colored General-Purpose Cable Ties Are 8" Long, With 18LB Of Tensile Strength For Professional Applications. They Are Made From Polyamide 6, 6 Nylon, Resulting In A High Mechanical Strength and A Wide Temperature Range (-40 F to 185 F). Fasten These Cables Ties Around A Wide Range Of Equipment With A Bundle Diameter Between .06" (1.5MM) and 2.09" (53MM), Using The Bent Tips and Serrated Locking Mechanism to Form An Effortless A
Weight per unit	1.3 (lbs/each)
Product Category	Tools & Testers
<b>Features</b>	
Warranty	1 YEAR
<b>Material, Color, and Finish</b>	
Finish	Natural



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	8" 18LB BULK NATURAL CBL TIE
extra long description	NSI GRP-818X Cable Tie 8 IN 18Lb Na
Features	PowerGRP cable ties are a comprehensive product line of specialty ties, strong enough to handle industrial environments and ideally suited for demanding applications. The GRP-818X ties combine a self-locking design with a general purpose 18lb tensile strength rating, guaranteeing that these ties won't break easily. The GRP in our name stands for Guaranteed Rugged and Powerful, just one way we show that we're fully committed to building strong ties for professional users. GRP-818X ties are waterproof an
Long Description	The PowerGRP GRP-818X 1000-Count Bulk Resealable Pack of Type 21 Natural-Colored General-Purpose Cable Ties are 8" long, with 18lb of tensile strength for professional applications. They're made from polyamide 6,6 nylon, resulting in a high mechanical strength and a wide temperature range (-40 F to 185 F). Fasten these cables ties around a wide range of equipment with a bundle diameter between .06" (1.5mm) and 2.09" (53mm), using the bent tips and serrated locking mechanism to form an effortless a
Product Type	Cable Tie 8 In 18LB Nat (1000PK)

## Manufacturer Information

Brand	Powergrp
GTIN	00662381009753
Manufacturers Part Number	GRP-818X
UPC	662381009753

## Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
----------------------	--

## Availability

minimum qty	1000
-------------	------

## Packaging

Carton	1
Package	1000
Weight Per each	1.26

## Uses, Certifications, and Standards

standard	UL62275
Temperature Rating	-40F to 185F