



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GUAX26SA 3/4" Alu Body&CVR *Crouse-Hinds*

Catalog Number	GUAX26SA
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Gua Conduit Outlet Box With Cover, 3" Cover Opening Diameter, Copper-Free Aluminum, X Shape, 3/4"
Weight per unit	1.4 (lbs/each)
Product Category	Alum

### Features

Cable Entry	(4) Side
dimensions	5.2500 IN X 2.0000 IN X 5.2500 IN

### Dimensions and Weight

Size	3/4 in
------	--------

### Descriptions

Construction	Explosionproof, Dust-Ignitionproof, Raintight
Description	3/4" ALU BODY&CVR
extra long description	CRS-H GUAX26 SA 3/4 AL OUTL BX 3 DI
Features	Crouse-Hinds series GUA and GUR explosionproof conduit outlet boxes are installed in conduit systems in hazardous areas to protect conductors in threaded rigid conduit, act as pull and splice boxes, change conduit direction, and provide access to conductors for maintenance and future system changes. GUA and GUR outlet boxes are certified for Class I, Division 1, Groups B, C, D and Class II, Division 1, Groups E, F, G. GUA boxes are available in ten different hub arrangements, maximizing flexibility in th
Long Description	Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover, 3" cover opening diameter, Copper-free aluminum, X shape, 3/4"
Product Type	3/4 Al Outl BX 3 Dia CVR THRD Rigid/lmc
Special Features	With Cover, Cover Opening Diameter 3 In

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274100500
Manufacturers Part Number	GUAX26 SA
UPC	782274100500

### Taxonomies, Classifications, and Categories

Category Description	HUB STYLE BOXES (GUAB, GUAT, ETC)
Type	Conduit outlet box with cover



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	1.35

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 886, CSA C22.2