



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL1447 Elastogrip Plug, 15A 125V, 5-15P *Hubbell Wiring Devices*

Catalog Number	HBL1447
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Male Plug, Elasto-Grip Dust Tight, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15P, Yellow, Single Pack.
Weight per unit	0.1500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15
connection	Screwed Terminal
Cord Type	All Portable
Current Rating	15
Material	Polycarbonate
Number of Wires	3-Wire
pallet quantity	4050
Phase	1
Poles	2-Pole
Voltage Rating	125
Wattage	1875;1875.0000
Wire Size	#18 to #12

Dimensions and Weight

Size	2.19 in x 1.55 in x 2.19 in
------	-----------------------------

Descriptions

Description	ELASTOGRIP PLUG, 15A 125V, 5-15P
extra long description	HWDK HBL1447 ELASTOGRIP PLUG, 15A 1
Long Description	Straight Blade Devices, Male Plug, Elasto-Grip Dust Tight, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15P, Yellow, Single Pack.
Product Type	Elastogrip Plug, 15A 125V, 5-15P
Special Features	Weatherproof Boot

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585013015
Manufacturers Part Number	HBL1447
series	Elastogrip
UPC	783585013015



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Commercial cord connectors
Type	PLUG

Packaging

Carton	10
Weight Per each	0.15

Uses, Certifications, and Standards

Application	Industrial/Commercial Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	5-15P
standard	CSA Certified to C22.2 No. 42 File 280;NEMA® WD-6 Compliant;UL Listed to UL498 File E1706