



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449



HBL8300HRED Dup RCPT, Com/HG, 20A 125V, 5-20R, RD *Hubbell Wiring Devices*

Catalog Number	HBL8300HRED
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Duplex, Compact Hospital Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5- 20R, Red, Single Pack.
Weight per unit	0.0780 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and Side Wired Screw Terminals
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	3-Wire
pallet quantity	3600
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	2500
Wire Size	#12 to #10

Dimensions and Weight

Size	3.28 in x 1.33 in x 1.05 in
------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449

Descriptions

Description	DUP RCPT, COM/HG, 20A 125V, 5-20R, RD
extra long description	HWDK HBL8300HRED DUP RCPT, COM/HG,
Features	HBL® Extra Heavy Duty Max Hospital Grade Devices - UL requirements for Hospital Grade devices is more stringent than those for standard devices. Hubbell receptacles are designed to meet and exceed the standards with Exclusive nickel-plated bypass contact design increases contact pressure, lowering the operating temperature; Four point grounding system provides redundant grounding for low resistance ground continuity in high abuse areas; Impact resistant deep face design prevents breakage. Because of these
Long Description	Straight Blade Devices, Receptacles, Duplex, Compact Hospital Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5- 20R, Red, Single Pack.
Product Type	Dup RCPT, Com/HG, 20A 125V, 5-20R, RD
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585247519
Manufacturers Part Number	HBL8300HRED
series	Hospital Grade
UPC	783585247519

Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	Duplex Receptacle

Packaging

Carton	1
Package	10
Weight Per each	0.078

Uses, Certifications, and Standards

Application	Hospital grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	CSA Certified, C22.2, No. 42 File 285;Fed. Spec. W-C-596;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186