



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBLEDLD524SEWUNV Hbledld524sewunvl850ed2u *Cooper Lighting Solutions*

|                  |                                                                                                                                                                                                                                                                                      |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | HBLEDLD524SEWUNV                                                                                                                                                                                                                                                                     |
| Manufacturer     | Cooper Lighting Solutions                                                                                                                                                                                                                                                            |
| Description      | Led High Bay Light, White Enamel, CRS;Aluminum, 120/277 V Ac, 0.542 A @ 277 V, 149 W, >60000 H Average Life, 22339 LM Brightness (Lumens), 5000 K, 70;80, Dimmable, Wide Beam Spread, Surface/Chain Mount, 48-1/2 In Length, 20-3/16 In Width, 2-3/8 In Height, 5 Yr Warranty, 24 LB |
| Weight per unit  | 24.0 (lbs/each)                                                                                                                                                                                                                                                                      |
| Product Category | Led Highbay Lighting                                                                                                                                                                                                                                                                 |

### Features

|                 |               |
|-----------------|---------------|
| amperage rating | 0.542 at 277V |
| Ballast Type    | N/A           |
| Lamp Type       | LED           |

### Material, Color, and Finish

|       |         |
|-------|---------|
| Style | (blank) |
|-------|---------|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | HBLEDLD524SEWUNVL850ED2U            |
| extra long description | CLS HBLED-LD5-24SE-W-UNV-L850-ED2-U |

### Manufacturer Information

|                           |                                |
|---------------------------|--------------------------------|
| Brand                     | METALUX                        |
| GTIN                      | 00080083788668                 |
| Manufacturers Part Number | HBLED-LD5-24SE-W-UNV-L850-ED2- |
| UPC                       | 080083788668                   |

### Taxonomies, Classifications, and Categories

|                      |                                           |
|----------------------|-------------------------------------------|
| Category Description | LED HIGHBAY, LOWBAY & INDUSTRIAL LIGHTING |
| Type                 | INDUSTRIAL                                |

### Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Weight Per each | 24 |

### Uses, Certifications, and Standards

|          |                                                         |
|----------|---------------------------------------------------------|
| Mounting | Surface Mount                                           |
| standard | cUL Listed - Damp Location;RoHS Compliant;DLC Qualified |