



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HCLR8 8A 600V Class CC Fast Acting Fuse

*Edison Fuses*

Catalog Number	HCLR8
Manufacturer	Edison Fuses
Description	Class CC Fast Acting Fuses 600V 8A - Class CC Fast Acting Fuses 600V Recommended For Non-Inductive Loads, Such As Lighting and Resistance Heating Circuits. Class CC Fast Acting Fuses 600V 8A Features Include: Rejection Type; For Both Standard Holders or Those Which Reject Other Type Fuses. Ir: 200KA RMS Sym; 10KA Ic (12-30A) UI 248-4 Class C meets UI 508 Paragraph 19.2.4 CSA Certified, Class HcI-CC CSA, C22.2 Class 1422-02 ORDER Qty Of 10 = 1 Box Of 10 BELOW Is More Info On Our Class CC Fast Acting Fuses 600V 8A:
Weight per unit	0.0200 (lbs/each)
Product Category	Renewable & Non-Renewable

### Features

amps	8
Fuse Type	Class CC Fast Acting Fuses
media	Yes
Voltage	600V



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	8A 600V CLASS CC FAST ACTING FUSE
extra long description	MOR T626-HCLR8 Class CC Fast Acting
Features	Edison offers a complete line of Class CC fuses to meet your circuit and equipment protection needs. These branch circuit rated compact fuses rated 600v, and delivering 200,000a IR Vac Sym provide excellent protection in the smallest package of any UL class of fuses. Choose from our EDCC time-delay fuses for your small horsepower motor circuits, our HCLR fast-acting for your non-inductive lighting and resistance heating loads or our HCTR time-delay fuses for your small control transformer protection.
Long Description	Class CC Fast Acting Fuses 600V 8A - Class CC Fast Acting Fuses 600V Recommended for non-inductive loads, such as lighting and resistance heating circuits. Class CC Fast Acting Fuses 600V 8A features include: Rejection type; for both standard holders or those which reject other type fuses. IR: 200kA RMS Sym; 10kA IC (12-30A) UL 248-4 Class CC Meets UL 508 paragraph 19.2.4 CSA Certified, Class HCRI-CC CSA, C22.2 Class 1422-02 Order Qty of 10 = 1 Box of 10 Below is more info on our Class CC Fast Acting Fuses 600V 8A:
Product Type	Class CC Fast Acting Fuses 600V 8a

## Manufacturer Information

Brand	Eaton
GTIN	00782634420804
Manufacturers Part Number	HCLR8
UPC	782634420804

## Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
----------------------	--------------

## Packaging

Carton	1
Package	10
Weight Per each	0.02