

Eaton HFD1030

Catalog Number: HFD1030

Eaton Series C complete molded case circuit breaker, F-frame, HFD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Single-pole, 30 A, 347 Vac, 125 Vdc, Load side, 50/60 Hz



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	HFD1030
	UPC
	786679175286
Product Length/Depth	Product Height
3.38 in	6 in
Product Width	Product Weight
1.38 in	1.63 lb
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel

Amperage Rating

30 A

Voltage rating

347 Vac, 125 Vdc

Trip Type

Fixed thermal, fixed magnetic

Circuit breaker type

HFD

Circuit breaker frame type

Complete breaker

Series

Series C

Terminals

Load side

Frame

F

Frequency rating

50/60 Hz

Interrupt rating

100 kAIC at 240 Vac

65 kAIC at 480 Vac

Number of poles

Single-pole

Resources

Application notes

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

Brochures

[Circuit breaker motor operators product aid](#)

[Motor protection circuit breakers product aid](#)

[MOEM MCCB Product Selection Guide](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[StrandAble terminals product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Breaker service centers](#)

[Counterfeit and Gray Market Awareness Guide](#)

Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Drawings

[Time Current Curves for Series C® F-Frame Circuit Breakers](#)

[F-frame Molded Case Circuit Breaker Drawing](#)

[HFD1 2D PDF](#)

[HFD1 2D Drawing Xchange](#)

[HFD1 3D Model Xchange](#)

[HFD1 3D Inventor](#)

Installation instructions

[Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[F-Frame 310+ Molded-case circuit breakers 15-225A](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[MOEM MCCB product selection guide](#)

[Series C F-Frame molded case circuit breakers](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)