

Eaton HFD2200

Catalog Number: HFD2200

Eaton Series C complete molded case circuit breaker, F-frame molded case circuit breaker, 200 A, Two-pole, Thermal magnetic trip



General specifications

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	HFD2200
	UPC
	786679015322
Product Length/Depth	Product Height
3.38 in	2.75 in
Product Width	Product Weight
2.75 in	4.5 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Amperage Rating

200 A

Voltage rating

600 Vac, 250 Vdc

Trip Type

Fixed thermal, fixed magnetic

Circuit breaker type

HFD

Circuit breaker frame type

Complete breaker

Series

Series C

Terminals

Load side

Frame

F

Frequency rating

50 to 60 Hz

Interrupt rating

65 kAIC at 480 Vac

100 kAIC at 240 Vac

Number of poles

Two-pole

Resources

Application notes

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

Brochures

[Motor protection circuit breakers product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[MOEM MCCB Product Selection Guide](#)

[Circuit breaker motor operators product aid](#)

[Multi-wire lugs product aid](#)

[StrandAble terminals product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Breaker service centers](#)

[Counterfeit and Gray Market Awareness Guide](#)

Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Drawings

[F-frame Molded Case Circuit Breaker Drawing](#)

[HFD2 3D Model Xchange](#)

[HFD2 2D Drawing Xchange](#)

[HFD2 3D Inventor](#)

[HFD2 2D PDF](#)

[Time Current Curves for Series C® F-Frame Circuit Breakers](#)

Installation instructions

[Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[Eaton Specification Sheet - HFD2200](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[MOEM MCCB product selection guide](#)

Series C F-Frame molded case circuit breakers

F-Frame 310+ Molded-case circuit breakers 15-225A

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)