

Eaton HJD3250F

Catalog Number: HJD3250F

Eaton Series C molded case circuit breaker frame, J-frame molded case circuit breaker frame, 250 A, Three-pole, Interchangeable thermal magnetic trip, HJD breaker



General specifications

Product Name	Catalog Number
Eaton Series C molded case circuit breaker frame	HJD3250F
	UPC
	786679512067
Product Length/Depth	Product Height
4.06 in	4.13 in
Product Width	Product Weight
4.13 in	12.5 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Type

Frame only

Amperage Rating

250 A

Voltage rating

600 Vac, 250 Vdc

Trip Type

Fixed thermal, fixed magnetic

Circuit breaker type

HJD

Circuit breaker frame type

Frame only

Series

Series C

Terminals

Line and load

Frame

J

Frequency rating

50 to 60 Hz

Terminal material

Aluminum

Interrupt rating

100 kAIC at 240 Vac

65 kAIC at 480 Vac

Number of poles

Three-pole

Resources

Application notes

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[UL listed 100%-rated molded case circuit breakers](#)

Brochures

[Plug-in adapters for molded case circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Circuit breaker motor operators product aid](#)

[MOEM MCCB Product Selection Guide](#)

[Motor protection circuit breakers product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[StrandAble terminals product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Breaker service centers](#)

Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Drawings

[J-frame Molded Case Circuit Breaker Drawing](#)

Multimedia

[Circuit breakers explained](#)

[Circuit Breakers Explained](#)

Specifications and datasheets

[Series C F-Frame molded case circuit breakers](#)

[Eaton Specification Sheet - HJD3250F](#)

[MOEM MCCB product selection guide](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[Series C, J-frame Time Current Curve](#)

Time/current curves

[Cutler-Hammer Series C Time-Current Curves for J-Frame Circuit Breakers](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)