



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3737 Grader Street Suite 120  
75041-0000, TX Garland  
Phone: 214-503-7227  
Fax: 214-503-9766



## HLA609FS5 6" Led Gimbal 27K/3K35K/4K/5K Canless 990L 120V

*Cooper Lighting Solutions*

Catalog Number	HLA609FS5
Manufacturer	Cooper Lighting Solutions
Description	6-Inch Super Adjustable Canless Led Gimbal, 990 Lumens At 3000K, 90 Plus Cri, Field Selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K, 120V 60HZ, Le & Te Phase Cut 100-5% Dimming, Matte White.
Weight per unit	1.4 (lbs/each)
Product Category	Lighting

### Features

amperage rating	0.085
Lamp Type	LED
Voltage Rating	120V, 60Hz

### Material, Color, and Finish

Style	(blank)
-------	---------

### Descriptions

Description	6" LED GIMBAL 27K/3K35K/4K/5K CANLESS 990L 120V
extra long description	CLS HLA609FS5 6" ADJUSTABLE HLA, 90
Long Description	6-inch Super Adjustable Canless LED Gimbal, 990 lumens at 3000K, 90 plus CRI, field selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K, 120V 60Hz, LE & TE phase cut 100-5% dimming, Matte White.
Product Type	6" Adjustable Hla, 900LM, 5CCT
Special Features	Round 3-, 4-, & 6-inch Super Adjustable Canless LED Gimbals

### Manufacturer Information

Brand	HALO
GTIN	00080083301249
Manufacturers Part Number	HLA609FS5
UPC	080083301249

### Taxonomies, Classifications, and Categories

Category Description	LED GENERAL PURPOSE LIGHTING
Type	HLA_Super Adjustable Canless Gimbal

### Packaging

Carton	1
Package	4
Weight Per each	1.35



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3737 Grader Street Suite 120  
75041-0000, TX Garland  
Phone: 214-503-7227  
Fax: 214-503-9766

## Uses, Certifications, and Standards

Application	lighting
Mounting	Direct Mount
standard	Energy Star;IC Rated;IECC Compliant;RoHS Compliant;Title 24 Compliant;UL Listed