

# Eaton HKD3350

Catalog Number: HKD3350

Eaton Series C complete molded case circuit breaker, K-frame, HKD, Fixed thermal, Fixed magnetic trip, Three-pole, 350 A, 600 Vac, 250 Vdc, 100 kAIC at 240 Vac, 65 kAIC at 480 Vac, Aluminum, Line and load, 50/60 Hz



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Series C complete molded case circuit breaker	HKD3350
	<b>UPC</b>
	786679319406
<b>Product Length/Depth</b>	<b>Product Height</b>
4.1 in	5.5 in
<b>Product Width</b>	<b>Product Weight</b>
5.5 in	8.5 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## defaultTaxonomyAttributeLabel

### Amperage Rating

350 A

### Voltage rating

600 Vac, 250 Vdc

### Trip Type

Fixed thermal, fixed magnetic

### Circuit breaker type

HKD

### Circuit breaker frame type

Complete breaker

### Series

Series C

### Shunt trip

208-380 Vac or 110-127 Vdc left pigtail rear

### Terminals

Line and load

### Frame

K

### Frequency rating

50 to 60 Hz

### Terminal material

Aluminum

### Interrupt rating

100 kAIC at 240 Vac

65 kAIC at 480 Vac

### Number of poles

Three-pole

## Resources

### Application notes

UL listed 100%-rated molded case circuit breakers

Application of Multi-Wire Terminals for Molded Case Circuit Breakers

Application of Tap Rules to Molded Case Breaker Terminals

### Brochures

Circuit breaker motor operators product aid

310+ MCCB product family pocket folder

MOEM MCCB Product Selection Guide

Current limiting Series C molded case circuit breakers product aid

Multi-wire lugs product aid

Motor protection circuit breakers product aid

Power metering and monitoring with Modbus RTU product aid

Plug-in adapters for molded case circuit breakers product aid

StrandAble terminals product aid

K-Frame 310+ Molded-case circuit breakers

Breaker service centers

### Catalogs

Eaton's Volume 4—Circuit Protection

Molded case circuit breakers catalog

### Drawings

HKD3 2D Drawing Xchange

HKD3 AutoCAD 2D Footprint

HKD3 3D Inventor

HKD3 AutoCAD 2D Footprint (mm)

HKD3 2D PDF

HKD3 3D Model Xchange

### Installation instructions

Installation Instructions for DK, KDB, KD, HKD, KDC, KW, HKW, KWC, CKD, CHKD Circuit Breakers and Molded Case Switches

Instruction Leaflet for the KES 310+ Electronic Trip Unit

### Multimedia

Circuit Breakers Explained

Circuit breakers explained

### Specifications and datasheets

F-Frame 310+ Molded-case circuit breakers 15-225A

Series C F-Frame molded case circuit breakers

Series C J-Frame molded case circuit breakers time current curves

Eaton Specification Sheet - HKD3350

MOEM MCCB product selection guide

Series C G-Frame molded case circuit breakers time current curves



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)