



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HLCEMS410FS1E 4" 12W Led Disk Light 27K/3K/35K/4K/5K W/Mot Sensr *Cooper Lighting Solutions*

Catalog Number	HLCEMS410FS1E
Manufacturer	Cooper Lighting Solutions
Description	4-Inch Led Disk Light With Integrated, 1065 Max Lumens, 90 Plus Cri, 5-Color Field-Selectable(TM) CCT 2700/3000/3500/4000/5000K, 10 Percent Phase Cut Le/Te Dimming, 120V 60HZ Matte White
Weight per unit	0.6300 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.1
Lamp Type	LED
Voltage Rating	120V, 60Hz

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	4" 12W LED DISK LIGHT 27K/3K/35K/4K/5K W/MOT SENSR
extra long description	CLS HLCEMS410FS1E HLCE MS 4IN,1000L
Long Description	4-inch LED Disk Light with Integrated, 1065 max lumens, 90 plus CRI, 5-color Field-Selectable(TM) CCT 2700/3000/3500/4000/5000K, 10 percent Phase Cut LE/TE Dimming, 120V 60Hz Matte White
Product Type	HLCE MS 4IN, 1000LM, 5CCT
Special Features	Round 4-inch and 6-inch low-profile surface mount disk lights with motion sensing

Manufacturer Information

Brand	HALO
GTIN	00080083303069
Manufacturers Part Number	HLCEMS410FS1E
UPC	080083303069

Taxonomies, Classifications, and Categories

Category Description	LED GENERAL PURPOSE LIGHTING
Type	HLCE Disk Light

Packaging

Carton	1
Package	4
Weight Per each	0.63



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	lighting
Mounting	Direct Mount
standard	Energy Star;IC Rated;IECC Compliant;RoHS Compliant;Title 20 Compliant;Title 24 Compliant;UL Listed