

Specifications

Photo is representative

Eaton HMCPE030H1C

Eaton molded case circuit breaker accessory motor protection, Motor circuit protector, 30 A, Three-pole, 480 V, Adjustable, Frame J-K, 90-300 A, 600 Y/347 V, Series G, Non-aluminum

General specifications

PRODUCT NAME	Eaton molded case circuit breaker accessory motor protection
CATALOG NUMBER	HMCPE030H1C
UPC	786679113660
PRODUCT LENGTH/DEPTH	2.99 in
PRODUCT HEIGHT	5.5 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	3 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	Contact Manufacturer
CERTIFICATIONS	UL Listed CSA Certified
GLOBAL CATALOG	HMCPE030H1C
PRODUCT TYPE	Molded case circuit breaker accessory



Powering Business Worldwide

Product specifications

AMPERAGE RATING	30 A
VOLTAGE RATING	480 V
TRIP TYPE	T98
FRAME SIZE	Frame J-K
MAGNETIC TRIP RANGE	90-300 A
VOLTAGE - MAX	600 Y/347 V
SERIES	Series G
TERMINAL MATERIAL	Non-aluminum
NUMBER OF POLES	Three-pole
TYPE	Motor circuit protector

Resources

APPLICATION NOTES

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Comprehensive circuit protection for control panel applications](#)

[Circuit breaker motor operators product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Series G MCCB quick selector](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

BROCHURES

[High performance operating handles for Series G circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Current limiting molded case circuit breaker module product aid](#)

[Motor protection circuit breakers product aid](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[StrandAble terminals product aid](#)

[Breaker service centers](#)

CATALOGS

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

MULTIMEDIA

[Flex shaft handle installation tutorial](#)

SPECIFICATIONS AND DATASHEETS

[MOEM MCCB product selection guide](#)

[Eaton Specification Sheet - HMCPE030H1C](#)

[NG and ND-Frame molded case circuit breakers](#)

WARRANTY GUIDES

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2026 Eaton. All Rights Reserved.