

Specifications



Photo is representative



Eaton HMCPJ250W5L

Eaton molded case circuit breaker accessory motor protection, Motor circuit protector, 250 A, Three-pole, Adjustable, Frame J-K, 1250-2500 A, 600 V, 250 Vdc, Series G, Line and load

General specifications

PRODUCT NAME	Eaton molded case circuit breaker accessory motor protection
CATALOG NUMBER	HMCPJ250W5L
UPC	782114965795
PRODUCT LENGTH/DEPTH	3.57 in
PRODUCT HEIGHT	7 in
PRODUCT WIDTH	4.13 in
PRODUCT WEIGHT	6 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	Contact Manufacturer
CERTIFICATIONS	UL Listed CSA Certified
GLOBAL CATALOG	HMCPJ250W5L
PRODUCT TYPE	Molded case circuit breaker accessory

Product specifications

AMPERAGE RATING	250 A
TRIP TYPE	T98
FRAME SIZE	Frame J-K
MAGNETIC TRIP RANGE	1250-2500 A
VOLTAGE - MAX	600 V, 250 Vdc
SERIES	Series G
TERMINALS	Line and load
NUMBER OF POLES	Three-pole
TYPE	Motor circuit protector

Resources

APPLICATION NOTES

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Comprehensive circuit protection for control panel applications](#)

[Series G MCCB quick selector](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[Current limiting molded case circuit breaker module product aid](#)

[StrandAble terminals product aid](#)

BROCHURES

[Plug-in adapters for molded case circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[Multi-wire lugs product aid](#)

[Motor protection circuit breakers product aid](#)

[High performance operating handles for Series G circuit breakers product aid](#)

[Breaker service centers](#)

CATALOGS

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

MULTIMEDIA

[Flex shaft handle installation tutorial](#)

SPECIFICATIONS AND DATASHEETS

[NG and ND-Frame molded case circuit breakers](#)

[Eaton Specification Sheet -
HMCPJ250W5L](#)

[MOEM MCCB product
selection guide](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton HMCPJ250W5L

Eaton molded case circuit breaker accessory motor protection, Motor circuit protector, 250 A, Three-pole, Adjustable, Frame J-K, 1250-2500 A, 600 V, 250 Vdc, Series G, Line and load

General specifications

PRODUCT NAME	Eaton molded case circuit breaker accessory motor protection
CATALOG NUMBER	HMCPJ250W5L
UPC	782114965795
PRODUCT LENGTH/DEPTH	3.57 in
PRODUCT HEIGHT	7 in
PRODUCT WIDTH	4.13 in
PRODUCT WEIGHT	6 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	Contact Manufacturer
CERTIFICATIONS	UL Listed CSA Certified
GLOBAL CATALOG	HMCPJ250W5L
PRODUCT TYPE	Molded case circuit breaker accessory

Product specifications

AMPERAGE RATING	250 A
TRIP TYPE	T98
FRAME SIZE	Frame J-K
MAGNETIC TRIP RANGE	1250-2500 A
VOLTAGE - MAX	600 V, 250 Vdc
SERIES	Series G
TERMINALS	Line and load
NUMBER OF POLES	Three-pole
TYPE	Motor circuit protector

Resources

APPLICATION NOTES

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Comprehensive circuit protection for control panel applications](#)

[Series G MCCB quick selector](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[Current limiting molded case circuit breaker module product aid](#)

[StrandAble terminals product aid](#)

BROCHURES

[Plug-in adapters for molded case circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[Multi-wire lugs product aid](#)

[Motor protection circuit breakers product aid](#)

[High performance operating handles for Series G circuit breakers product aid](#)

[Breaker service centers](#)

CATALOGS

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

MULTIMEDIA

[Flex shaft handle installation tutorial](#)

SPECIFICATIONS AND DATASHEETS

[NG and ND-Frame molded case circuit breakers](#)

[Eaton Specification Sheet -
HMCPJ250W5L](#)

[MOEM MCCB product
selection guide](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

