



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IOPA4P32LWN35M (4) F32T8 120-277V Elec Bal *Advance By Signify*

| | |
|------------------|--|
| Catalog Number | IOPA4P32LWN35M |
| Manufacturer | Advance By Signify |
| Description | Reliable and Energy Efficient Philips Advance'S Centium Commercial Grade Specifications, Plus Added Benefits Of Lamp Striation Reduction Technology. |
| Weight per unit | 0.8000 (lbs/each) |
| Product Category | Electronic Linear Fluorescent |

Features

| | |
|------------------------------|--------------|
| amperage rating | 0.81-0.35 |
| ANSI Code | N/A |
| Ballast Factor | 0.77 |
| dimnable | Non Dimmable |
| Lamp Type | Fluorescent |
| Minimum Starting Temperature | -20 |
| Number of Lamps | 4 |
| Power Factor | 0.98 |
| start type | Instant |
| total harmonic distortion | <=10 |
| Voltage Rating | 120-277 |
| Wattage | 96-94 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|--------|------|
| Height | 3.94 |
| Length | 3.74 |
| Width | 5.12 |

Descriptions

| | |
|------------------------|--|
| Description | (4) F32T8 120-277V ELEC BAL |
| extra long description | ADV 500116 ELE BALLAST (4) F32T8 12 |
| Long Description | Reliable and energy efficient Philips Advance's Centium commercial grade specifications, plus added benefits of lamp striation reduction technology. |
| Product Type | Ele Ballast (4) F32T8 120-277V |
| Special Features | IntelliVolt 120-277V, Parallel Lamp Operation |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | Signify Electronics |
| GTIN | 00781087115275 |
| Manufacturers Part Number | IOPA4P32LWN35M |
| UPC | 781087115275 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | ELECTRONIC BALLAST |
| Type | ELECTRONIC |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 0.8 |

Uses, Certifications, and Standards

| | |
|----------------------|--|
| Application | Commercial |
| Frequency Rating | 50to60 |
| Mounting standard | 8.9 CSA certificate;UL certificate;CEC Listing;CEE Rated;NEMA Premium;RoHS Compliant |