ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

IHP30H 30" Circulator Fan

Tpi Corp. (Raywall)

Catalog Number	IHP30H
Manufacturer	Tpi Corp. (Raywall)
Description	Industrial Assembled Circulator Heads and Mount, High Performance, Size- 33.5 In, Blade Size- 30 In, Flow Rate- 6200 (Low), 8200 (High) CFM, 1/3 HP, 3 Amp, Speed- 800 (Low), 1100 (High) RPM, 120 V, 2 Speeds
Weight per unit	42.0 (lbs/each)
Product Category	Fans - Industrial & Commercial

Features

amperage rating	3
Blade Size	30 IN
Drive Type	Motor
flow rate	6200 (Low);8200 (High) CFM
horsepower	0.333
Number of Speeds	2
Phase	1
shaft diameter	1/2 IN
Voltage Rating	120

Material, Color, and Finish

Housing Material	Steel
Style	Paddle Blade

Dimensions and Weight

Size	33.5 IN

Descriptions

Description	30" CIRCULATOR FAN
extra long description	TPI IHP30H 30" Asmbld Ind. High Per
Long Description	Industrial Assembled Circulator Heads and Mount, High Performance, Size- 33.5 IN, Blade Size- 30 IN, Flow Rate- 6200 (Low), 8200 (High) CFM, 1/3 HP, 3 AMP, Speed- 800 (Low), 1100 (High) RPM, 120 V, 2 Speeds
Product Type	30" Asmbld Ind. High Perf Head 1/3 HP
Special Features	Features: Pull Chain Switch;Steel Hub/Spider Aluminum Paddle Blades;Coated Steel Guards;3 Year Warranty;Totally Enclosed;Permanent Split Capacitor;Permanently Lubricated; Blade Material: Aluminum; Cord Type: 3 Conductor SJT; Cord Length: 12 FT

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	TPI
GTIN	00686334798990
Manufacturers Part Number	IHP30H
UPC	686334798990

Taxonomies, Classifications, and Categories

Type	Assembled High Performance

Packaging

Carton	1
Weight Per each	42

Uses, Certifications, and Standards

Application	Indoor-Industrial
Mounting	Pedestal/Wall/I-Beam/Ceiling/Suspension/Pole
standard	cETLus Listed;OSHA