


Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685





IPL104 1/0-#14 4 Pole Polaris Connector Block Nsi Industries

Catalog Number	IPL104		
Manufacturer	Nsi Industries		
Description	The Polaris IPL1/0-4 Multi-Tap Single Side Entry Connector Features 4 Ports Sized For 1/0-14 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including Installation In Cable Trays, Panel Boards,		
Weight per unit			
Product Category	Large Terminals & Connectors		
Features			
Number of Conductors	4		
Poles	1		
Voltage Rating	600 V		
Warranty	1 YEAR		
Wire Size	1/0-14 AWG		
Wire Type	Class B & C		
Material, Color, and Finish			
Color	Black		
Finish	Plastisol Insulated		
Housing Material	Aluminum		
Dimensions and Weight			
Size	L=2.890 - W=1.500 - H=1.688		



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

_			
\mathbf{I}	CCPI	nti	ons
	~ 1 1 1		
-	JULI	\sim u	VIIJ
_			_

Descriptions			
Description	1/0-#14 4 POLE POLARIS CONNECTOR BLOCK		
extra long description	NSI IPL1/0-4 POLARIS Ins Multi-Tap The Polaris IPL1/0-4 4-Port Single-Side Connector provides the simplest solution for forming a secure connection between up to four conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 1/0-14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric strength		
Features			
Long Description	The Polaris IPL1/0-4 Multi-Tap Single Side Entry Connector features 4 ports sized for 1/0-14 AWG wires. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including installation in cable trays, panel boards,		
Product Type	Polaris Ins Multi-Tap 1/0 4 Port Sse		
Special Features	(4) 1/0-14 AWG - Dual Rated		
Manufacturer Information			
Brand	Polaris		
GTIN	00662381911025		
Manufacturers Part Number	IPL1/0-4		
UPC	662381911025		
Taxonomies, Classifications, and C	Categories		
Category Description	CDLIT DOLTC		
Туре	Single Sided Entry		
Packaging			
Carton	6		
Weight Per each	0.26		
Uses, Certifications, and Standard	S		
Application	Wire Termination		
environmental conditions	90 C		
standard	UL 486A/B		