



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IPL43C 4-14AWG 3PRT Insld Tap Conn

*Nsi Industries*

Catalog Number	IPL43C
Manufacturer	Nsi Industries
Description	The Polaris IPL4-3C Multi-Tap Single Side Entry Vision Tap Connector Features 3 Ports Sized For 4 - 14 Awg Wires. The Clear Body Allows Users to See Their Conductor Placement and Is Wrapped In A Layer Of Plastisol Insulation. Each Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including In
Weight per unit	0.0800 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

Number of Conductors	3
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	4-14 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Clear
Finish	Plastisol Insulated
Housing Material	Aluminum

### Dimensions and Weight

Size	L=1.550 - W=1.188 - H=1.375
------	-----------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	4-14AWG 3PRT INSLTD TAP CONN
extra long description	NSI IPL4-3C Polaris Vision Tap (Cle
Features	The Polaris IPL4-3C 3-Port Single-Side Connector provides the simplest solution for forming a secure connection between up to three conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 4 - 14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The clear body lets installers see their work for optimal condu
Long Description	The Polaris IPL4-3C Multi-Tap Single Side Entry Vision Tap Connector features 3 ports sized for 4 - 14 AWG wires. The clear body allows users to see their conductor placement and is wrapped in a layer of plastisol insulation. Each port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including in
Product Type	Polaris Vision Tap (Clear) 4-14 Awg Polaris Insulated Multi-
Special Features	(3) 4-14 AWG - Dual Rated

## Manufacturer Information

Brand	Polaris
GTIN	00662381996442
Manufacturers Part Number	IPL4-3C
UPC	662381996442

## Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Single Sided Entry

## Packaging

Carton	12
Weight Per each	0.08

## Uses, Certifications, and Standards

Application	Wire Termination
Enclosure	Clear Plastisol
environmental conditions	Dry Location Only
standard	UL 486A/B