



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7929 N Sam Houston Pkwy W Suite 100
77064-0000, TX Houston
Phone: 281-345-1143
Fax: 281-345-7697



IPLD306 3/0 6 Port *Nsi Industries*

Catalog Number	IPLD306
Manufacturer	Nsi Industries
Description	The Polaris IPLD3/0-6 Multi-Tap Dual-Sided Entry Connector Features 6 Ports Sized For 3/0 - 6 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Dual-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including Installation In Cable Trays, Pa
Weight per unit	0.6200 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Aluminum
Number of Conductors	6
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	3/0-6 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated

Dimensions and Weight

Size	L=4.970 - W=1.830 - H=1.790
------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7929 N Sam Houston Pkwy W Suite 100
77064-0000, TX Houston
Phone: 281-345-1143
Fax: 281-345-7697

Descriptions

Description	3/0 6 PORT
extra long description	NSI IPLD3/0-6 3/0-6 Awg Polaris In
Features	The Polaris IPLD3/0-6 6-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to six conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 3/0 - 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric strength
Long Description	The Polaris IPLD3/0-6 Multi-Tap Dual-Sided Entry Connector features 6 ports sized for 3/0 - 6 AWG wires. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each dual-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including installation in cable trays, pa
Product Type	3/0-6 Awg Polaris Insulated Multi-Tap Conn 6 Port (Dual Sid
Special Features	(6) 3/0-6 AWG - Dual Rated

Manufacturer Information

Brand	Polaris
GTIN	00662381927040
Manufacturers Part Number	IPLD3/0-6
UPC	662381927040

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Double Sided Entry

Packaging

Carton	4
Weight Per each	0.62

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B
Temperature Rating	90 C