


ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9139 Linwood Ave 71106-0000, LA Shreveport Phone: 318-688-9822 Fax: 318-688-0702





IPCS1010 1/0-8, 1/0-8 Insulation Piercing Connector *Nsi Industries*

Catalog Number	IPCS1010
Manufacturer	Nsi Industries
Description	Insulation Piercing Connector 1/0 - 8 Awg Insulation Piercing Connectors Are Made For Use With Copper-Copper, Copper to Aluminum and Aluminum to Aluminum Applications. They Are Safe to Use and Are Completely Insulated, No Need to Strip Wire They Can Be Installed On Energized Conductors With No Contact At Any Point. No Spacer Required Between Connections. Exclusive "Turbo Spacer" Keeps Tap Side Open While Main Conductor Is Being Tightened. Watertight
Weight per unit	
Product Category	
Features	
amperage rating	190 (CU Amps) - 150 (AL Amps)
Conductor Size	1 (0 0 A)A(C (Main)
Material	Fibor Doinforced Thomas I Dioatic
Tap Size	4/0.0 ANNO
Voltage Rating	
Warranty	
Material, Color, and Finish	
Color	Black
Finish	Thermal Plastic
Dimensions and Weight	
Size	L=2.20 - W=1.80 - H=3.10



Packaging

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9139 Linwood Ave 71106-0000, LA Shreveport Phone: 318-688-9822

Fax: 318-688-0702

Descriptions	
Description	1/0-8, 1/0-8 INSULATION PIERCING CONNECTOR
extra long description	NSI IPCS1010 Insulation Piercing Co
Features	Insulation Piercing Connector 1/0 - 8 AWG Insulation piercing connectors are made for use with copper-copper, copper to aluminum and aluminum to aluminum applications. They are safe to use and are completely insulated, no need to strip wire. They can be installed on energized conductors with no contact at any point. No spacer required between connections. Exclusive "turbo spacer" keeps tap side open while main conductor is being tightened. Watertight
Long Description	Insulation Piercing Connector 1/0 - 8 AWG Insulation piercing connectors are made for use with copper-copper, copper to aluminum and aluminum to aluminum applications. They are safe to use and are completely insulated, no need to strip wire. They can be installed on energized conductors with no contact at any point. No spacer required between connections. Exclusive "turbo spacer" keeps tap side open while main conductor is being tightened. Watertight
Product Type	Insulation Piercing Connector 1/0-1/0 Aw
Special Features	No need to strip wire - No tape or cover needed - Exclusive turbo spacer keeps tap side open while main conductor is being tightened
Manufacturer Information	
Brand	NSi
GTIN	00662381082633
Manufacturers Part Number	IPCS1010
UPC	662381082633
Taxonomies, Classifications, and	Categories
Category Description	SPLIT BOLTS
Туре	Insulation Piercing Connectors

Carton	
Package	6
Weight Per each	0.3
es, Certifications, and Standards	
Application	NSI
environmental conditions	90 C
Mounting	Clamp
standard	UL486B Listed
Temperature Rating	90 C