



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IZT2PSP32SC35I 2-F32T8 120/277 (24) Dim Bal

Advance By Signify

Catalog Number	IZT2PSP32SC35I
Manufacturer	Advance By Signify
Description	Maximum Dimming Versatility Compatible With Controls From Numerous Manufacturers Using Standard 0-10VDC Controls; Ideal For Frequent Switching Applications Such As Occupancy Sensors and Daylight Harvesting - Programmed Start Operation The Mark 7 0-10V Series Of Dimmable Electronic Ballasts Offer Maximum Versatility By Incorporating Separate Control Leads For Use With A Wide Array Of Controllers, Including Occupancy Sensors, Daylight Harvesting Controls, and Building Management Systems From More Than 40 Manu
Weight per unit	1.0 (lbs/each)
Product Category	20150307134717

Features

Ballast Factor	1.00
dimnable	Yes
Lamp Type	T8 RS
Number of Lamps	2
Power Factor	0.99
Power Rating	32
start type	Programmed Start
Voltage Rating	120-277

Dimensions and Weight

Height	4.65
Length	3.74
Width	6.69



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	2-F32T8 120/277 (24) DIM BAL
extra long description	ADV 505123 ELE DIMMING BALLAST (2)
Long Description	Maximum dimming versatility Compatible with controls from numerous manufacturers using standard 0-10VDC controls; Ideal for frequent switching applications such as occupancy sensors and daylight harvesting - Programmed start operation The Mark 7 0-10V series of dimmable electronic ballasts offer maximum versatility by incorporating separate control leads for use with a wide array of controllers, including occupancy sensors, daylight harvesting controls, and building management systems from more than 40 manu
Product Type	Ele Dimming Ballast (2) F32T8 120-277V

Manufacturer Information

Brand	Signify Electronics
GTIN	00781087134849
Manufacturers Part Number	505123
UPC	781087134849

Taxonomies, Classifications, and Categories

Category Description	DIMMING BALLASTS
----------------------	------------------

Packaging

Carton	1
Weight	1
Weight Per each	1

Uses, Certifications, and Standards

Application	Lighting Luminaire Component
Frequency Rating	50to60
standard	CSA certificate;UL certificate;CEC Listing;CEE Rated;CSA E;NEMA Premium;RoHS Compliant