



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IPLD7503 750-250 2S 3 Multi Cable Insul Tap

Nsi Industries

| | |
|------------------|--|
| Catalog Number | IPLD7503 |
| Manufacturer | Nsi Industries |
| Description | The Polaris IPLD750-3 Multi-Tap Dual-Sided Entry Connector Features 3 Ports Sized For 750 - 250 MCM Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Dual-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including Installation In Cable Trays, |
| Weight per unit | 1.4 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------------------|-------------|
| Number of Conductors | 3 |
| Poles | 1 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |
| Wire Size | 750-250 MCM |
| Wire Type | Class B & C |

Material, Color, and Finish

| | |
|------------------|---------------------|
| Color | Black |
| Finish | Plastisol Insulated |
| Housing Material | Aluminum |

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | L=4.950 - W=3.410 - H=3.420 |
|------|-----------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 750-250 2S 3 MULTI CABLE INSUL TAP |
| extra long description | NSI IPLD750-3 750-250 Mcm Non -UI P |
| Features | The Polaris IPLD750-3 3-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to three conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 750 - 250 MCM wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric stren |
| Long Description | The Polaris IPLD750-3 Multi-Tap Dual-Sided Entry Connector features 3 ports sized for 750 - 250 MCM wires. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each dual-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including installation in cable trays, |
| Product Type | 750-250 MCM Non -UI Polaris Insulated Multi-Tap Conn 3 Port |
| Special Features | (3) 750-250 MCM - Dual Rated |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Polaris |
| GTIN | 00662381926012 |
| Manufacturers Part Number | IPLD750-3 |
| UPC | 662381926012 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | SPLIT BOLTS |
| Type | Double Sided Entry |

Packaging

| | |
|-----------------|--------|
| Carton | 3 |
| Weight Per each | 1.3999 |

Uses, Certifications, and Standards

| | |
|--------------------------|------------------|
| Application | Wire Termination |
| environmental conditions | 90 C |
| standard | UL 486A/B |