



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6 South Hickory  
71373-0000, LA Vidalia  
Phone: 318-336-5113  
Fax: 318-336-5587



## IPLMD3503 350-#6 3 Pole Polaris Connector Block W/MTG Holes

*Nsi Industries*

Catalog Number	IPLMD3503
Manufacturer	Nsi Industries
Description	The Polaris IPLMD350-3 Multi-Tap Mountable Dual-Sided Entry Connector Features 3 Ports Sized For 350 MCM - 6 Awg Wires. Mounting Holes On Either Side Of The Connector Allow For Direct Mounting to Troughs, Panels or Wireways With 1/4" Bolts. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Dual-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, With
Weight per unit	0.9500 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Number of Conductors	3
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	350 MCM-6 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated
Housing Material	Aluminum

### Dimensions and Weight

Size	L=5.120 - W=2.410 - H=2.770
------	-----------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6 South Hickory  
71373-0000, LA Vidalia  
Phone: 318-336-5113  
Fax: 318-336-5587

## Descriptions

Description	350-#6 3 POLE POLARIS CONNECTOR BLOCK W/MTG HOLES
extra long description	NSI IPLMD350-3 350 Mcm - 6 Awg Pola
Features	The Polaris IPLMD350-3 3-Port Dual-Sided Mountable Connector provides the simplest solution for forming a secure connection between up to three conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 350 MCM - 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. Mountable connectors feature 1/4" mounting hol
Long Description	The Polaris IPLMD350-3 Multi-Tap Mountable Dual-Sided Entry Connector features 3 ports sized for 350 MCM - 6 AWG wires. Mounting holes on either side of the connector allow for direct mounting to troughs, panels or wireways with 1/4" bolts. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each dual-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, with
Product Type	350 MCM - 6 Awg Polaris Insulated Multi-Tap Conn 3 Port (Dua
Special Features	(3) 350 MCM-6 AWG - Dual Rated - With Mounting Holes

## Manufacturer Information

Brand	Polaris
GTIN	00662381944016
Manufacturers Part Number	IPLMD350-3
UPC	662381944016

## Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Double Sided Entry With Mounting Holes

## Packaging

Carton	2
Weight Per each	0.95

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B