



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



J20009NECRTP Lineman'S Pliers, Fish Tape Pull/Crimping, 9"

Klein Tools

Catalog Number	J20009NECRTP
Manufacturer	Klein Tools
Description	Side-Cutting Plier, Steel Blade Material, 25/32 In Blade Length, Blue/Black (Handle), Journeyman (Handle), 9-1/2 In Overall Length, 1-19/32 In Jaw Length, 1-1/14 In Jaw Width, 1.13 LB
Weight per unit	1.1 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

Features

Handle Length	5.55" (14.1 cm)
jaw thickness	0.625" (1.6 cm)
Jaw Type	Flat
knife length	0.797" (2 cm)
Material	Steel
media	Yes
Overall Height	0.75" (1.9 cm)
Overall Width	2.06" (5.2 cm)
tether capable	No

Material, Color, and Finish

Handle Color	LIGHT BLUE/BLACK
--------------	------------------

Descriptions

Also Known As...	Linesman's Pliers Rabbit Ears Pliers Loppers Diagonal cutters
Description	LINEMAN'S PLIERS, FISH TAPE PULL/CRIMPING, 9"
extra long description	KLEIN J2000-9NECRTP High Leverage S
Features	These Klein Tools Lineman's Pliers are induction hardened and have a hot-riveted joint for smooth and powerful action without handle wobble. Their unique tempered handle design, with dual material Journeyman handles provide a better grip and absorbs the snap when cutting wire, screws, nails or ACSR. These side-cutting pliers also have cross-hatched knurled jaws, and built in channels for pulling fish tapes without damage.
similar brands	kleins

Manufacturer Information

GTIN	00092644721243
UPC	092644721243



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	High Leverage Side Cutting/Pulling Pliers

Packaging

Carton	1
Package	6
Weight Per each	1.1

Uses, Certifications, and Standards

Application	ACSR, Screws, Nails, Most Hardened Wire;Crimps Noninsulated Connectors, Lugs and Terminals;Pulls Steel Fish Tape
standard	Y