



**VARIETY
OF TRIMS
AVAILABLE!**

Low-profile junction box downlight



The HALO JBD Slim Surface Mount Downlight is a 4-inch low-profile fixture designed for easy and fast installation in residential applications. The HALO JBD features a variety of easily interchangeable designer trims in various styles and color finishes to match any aesthetic and installs in most 4-inch standard junction boxes

Product Features

- Available in 4" with interchangeable round, square, and full-lensed designer trims in multiple finishes
- Installs in most standard 4" junction boxes
- 5-color field-selectable CCTable: 2700K, 3000K, 3500K, 4000K, 5000K; 90+ CRI
- Slim, plastic non-conductive dead-front trim with smooth flat lens
- Up to 700 lumens delivered
- 5% phase cut LE/TE dimming (120V input) with compatible controls
- Wet location listed for showers and covered outdoor areas
- Air-Tite, IC-rated, and ENERGY STAR® certified
- 50,000 life hours
- 5-Year Warranty




LEARN MORE

Low profile design: ultra slim design sits flush with the ceiling for a modern, sleek aesthetic



SeleCCTability

5-color field selectable color temperatures between warm (2700K) to daylight (5000K) for increased flexibility and reduced sku count.



Compatibility

The JBD4 also includes alternate mounting hardware for 4" recessed housings. (non-California version)

- Wire fixture to Edison adapter
- Use included extension springs to attach fixture to the housing



Catalog Number	Material Number	Description	UPC
----------------	-----------------	-------------	-----

LED Fixture*

JBD4079FS1EWH	13646662	4" JBD, 700lm, 5CCT, 120V, Matte White	080083283514
JBD4079FS1EWH-CA	13650608	4" JBD, 700lm, 5CCT, 120V, Matte White, California compliant	080083285631

*Round paintable matte white designer trim included.

Round Designer Trims

JBD4TRMMW	13646663	4" JBD Round Flat Designer Trim, Paintable Matte White	080083283538
JBD4TRMSN	13646664	4" JBD Round Flat Designer Trim, Satin Nickel	080083283552
JBD4TRMTBZ	13646665	4" JBD Round Flat Designer Trim, Tuscan Bronze	080083283576
JBD4TRMMB	13646666	4" JBD Round Flat Designer Trim, Matte Black	080083283590
JBD4TRMMWB	13664342	4" JBD Round Baffle Designer Trim, Paintable Matte White	080083291311
JBD4TRMSNB	13664343	4" JBD Round Baffle Designer Trim, Satin Nickel	080083291335
JBD4TRMTBZB	13664344	4" JBD Round Baffle Designer Trim, Tuscan Bronze	080083291359
JBD4TRMMBB	13664345	4" JBD Round Baffle Designer Trim, Matte Black	080083291373

Round Full Lens Diffuser

JBD4DIFF	13646667	4" JBD Round Designer Trim, Full Lens Diffuser	080083283613
-----------------	----------	--	--------------

Square Designer Trims

JBD4STRMMW	13650729	4" JBD Square Flat Designer Trim, Paintable Matte White	080083285679
JBD4STRMSN	13650740	4" JBD Square Flat Designer Trim, Satin Nickel	080083285693
JBD4STRMTBZ	13650741	4" JBD Square Flat Designer Trim, Tuscan Bronze	080083285716
JBD4STRMMB	13650742	4" JBD Square Flat Designer Trim, Matte Black	080083285730
JBD4STRMMWB	13664346	4" JBD Square Baffle Designer Trim, Paintable Matte White	080083291397
JBD4STRMSNB	13664347	4" JBD Square Baffle Designer Trim, Satin Nickel	080083291410
JBD4STRMTBZB	13664348	4" JBD Square Baffle Designer Trim, Tuscan Bronze	080083291434
JBD4STRMMBB	13664349	4" JBD Square Baffle Designer Trim, Matte Black	080083291458

Customizable

Interchangeable overlays in a variety of styles and finishes

Round Designer Trims



JBD4TRMMW
Paintable
Matte White




JBD4TRMSN
Satin Nickel




JBD4TRMTBZ
Tuscan Bronze



JBD4TRMMB
Matte Black



JBD4TRMMWB
Paintable
Matte White



JBD4TRMSNB
Satin Nickel



JBD4TRMTBZB
Tuscan Bronze



JBD4TRMMBB
Matte Black

Square Designer Trims



JBD4STRMMW
Paintable
Matte White



JBD4STRMSN
Satin Nickel



JBD4STRMTBZ
Tuscan Bronze



JBD4STRMMB
Matte Black



JBD4STRMMWB
Paintable
Matte White



JBD4STRMSNB
Satin Nickel



JBD4STRMTBZB
Tuscan Bronze



JBD4STRMMBB
Matte Black

Round Full Lens Diffuser



JBD4DIFF
Full Lens Diffuser



Refer to ENERGY STAR® Certified Products List. Can be used to comply with California Title 24 High Efficacy requirements. Certified to California Appliance Efficiency Database under JA8.

Lighting Brands

Ametrix
AtLite
Corelite
Ephesus
Fail-Safe
HALO
HALO Commercial
Invue
iO
Iris
Lumark
Lumière
McGraw-Edison
Metalux
MWS
Neo-Ray
Portfolio
PrentaLux - 3D Printed Lighting
RSA
Shaper
Streetworks
Sure-Lites
Telensa

Controls Brands

Greengate
Fifth Light
Intelligent Lighting Controls

**Connected Lighting Systems
and Smart Spaces Platform**

WaveLinx



Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2024 Cooper Lighting Solutions
All Rights Reserved
Printed in USA
Publication No. BR51861123
May 2, 2024 4:34 PM

All other trademarks are property
of their respective owners.

Product availability, specifications,
and compliances are subject to
change without notice.