

Eaton JD3225

Catalog Number: JD3225

Eaton Series C complete molded case circuit breaker, J-frame, JD, Complete breaker, Fixed thermal, Fixed magnetic trip, Three-pole, 225 A, 600 Vac, 250 Vdc, 65 kAIC at 240 Vac, 35 kAIC at 480 Vac, Aluminum, Line and load, 50/60 Hz



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	JD3225
	UPC
	786679346167
Product Length/Depth	Product Height
4.06 in	4.13 in
Product Width	Product Weight
4.13 in	9.55 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Type

Complete breaker

Amperage Rating

225 A

Voltage rating

600 Vac, 250 Vdc

Trip Type

Fixed thermal, fixed magnetic

Circuit breaker type

JD

Circuit breaker frame type

Complete breaker

Series

Series C

Terminals

Line and load

Frame

J

Frequency rating

50 to 60 Hz

Terminal material

Aluminum

Interrupt rating

35 kAIC at 480 Vac

65 kAIC at 240 Vac

Number of poles

Three-pole

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

Brochures

[Circuit breaker motor operators product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[MOEM MCCB Product Selection Guide](#)

[StrandAble terminals product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Motor protection circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Breaker service centers](#)

Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Drawings

[J-frame Molded Case Circuit Breaker Drawing](#)

[JD3 2D Drawing Xchange](#)

[JD3 2D PDF](#)

[JD3 3D Model Xchange](#)

[JD3 3D Inventor](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[Series C J-Frame molded case circuit breakers time current curves](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[MOEM MCCB product selection guide](#)

[Eaton Specification Sheet - JD3225](#)

[Series C, J-frame Time Current Curve](#)

[Series C F-Frame molded case circuit breakers](#)

Time/current curves

[Cutler-Hammer Series C Time-Current Curves for J-Frame Circuit Breakers](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)